BOLT, SHOULDER EYE, 3/4in x 8in

By Chance
Catalog # PSSE3408CW

*Representative Image

Shoulder eye bolts are used to support suspension insulators in deadend applications. The flat base of the eye functions as a washer to protect structure of the wood member.

Features

- 4" thread length
- Includes one square nut and cone pointed end
- Rated tensile strength is 22,000 lbs.
- Galvanized per CSA G164-M
- Manufactured in compliance with Canadian CSA C83-96 specification and Charpy level 1 impact properties with average minimum energy absorption of 20 joules when tested at -20 degrees C per ASTM A370

General

Catalog Number	PSSE3408CW
Coating	Galvanized, CSA G164-M
Material	Steel
Tensile Strength	22000 lb.
UPC	096359573388

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Distance From Pole	N/A
Length	8 in
Length - Threaded Area	4 in
Weight	0 lb

Certifications And Compliance

Industry Standard(s)	CSA C83.67

Logistics

Carton Quantity	20

Product Assets

Catalogs - Fasteners - Canadian Standard (CSA)
Sales Drawings - Shoulder Eye Bolts, 3/4 (CW)
Specifications - PSSE3408CW

©2024 Hubbell Incorporated. All rights reserved