


Power and AV Boxes

4" & 4 1/16" Square boxes

Mud rings, covers, supports

Steel adjustable mud rings provide flexibility after installation to match the drywall depth. Hinged mud rings allow devices to be installed during pre-assembly, then swing out of the way for final wiring on site. Protector plates can be attached during prefab to protect devices during drywall install, then removed during trim out.

- 1 & 2-Gang adjustable mud rings
- Standard 1 & 2-gang mud rings
- Adjustable open box mounting brackets
- Floor mounted box support includes fold back stabilizer prevents bracket from being pushed back in wall cavity during drywall installation



Mud Rings

For use with	Type	Raised Height	Capacity (In. ³)	Listing	Catalog Number	
4 1/16" boxes	1-Gang, Adjustable	1/2" to 1 3/8"	4 to 9.5	UL Listed	HBL868AMR HBL869AMR	
	2-Gang, Adjustable		8 to 15.5			
	1-Gang	2-Gang	5/8"	4.5	cULus	HBL843 HBL842 HBL841 HBL818 HBL840 HBL819 HBL820
			1 1/4"	9.5		
			1/2"	5.5		
			5/8"	7.3		
4" boxes	1-Gang, Adjustable	1/2" to 1 3/8"	4 to 9.5	UL Listed	HBL768AMR HBL769AMR	
	2-Gang, Adjustable		8 to 15.5			
	1-Gang	5/8"	4.5	UL Listed	HBL768	
	1-Gang, Stud Mount	5/8"	4.5	UL Listed	HBL768B	
	1-Gang, Hinged	5/8"	5.5	UL Listed	HBL768H	
	1-Gang	1 1/4"	9.5	cULus	HBL775	
	2-Gang	5/8"	7.3	cULus	HBL769	
	2-Gang, Stud Mount	5/8"	7.3	UL Listed	HBL769B	
	2-Gang, Hinged	5/8"	8.3	UL Listed	HBL769H	
	2-Gang	1 1/4"	15	cULus	HBL781	

Square Metallic Covers for Exposed Work

For use with	1 Decorator	1 Duplex	2 Decorator	2 Duplex	1 Duplex, 1 Decorator
4" boxes, UL Listed	HBL808C	HBL902C	HBL809C	HBL907C	HBL915C

Metallic Box Brackets and Supports

For use with	Type	Box Mounting	Catalog Number
4 1/16" and 4" boxes, cULus	Open Wall Adjustable Box Bracket	16" to 24"	HBL9020R
	Floor Mounted Box Support	12"	HBL9009
		18"	HBL9010

Plates

Description	For use with	Height	1-Gang	2-Gang
Reusable metallic mud ring cable protector plate	4 1/16" and 4" boxes	Flush 3/4"	HBL701F HBL701R	HBL702F HBL702R
Metallic flush-fit devices levelling plate	4 1/16" and 4" boxes	-	HBL999	—

Dimensions in Inches (mm)