



SNAPConnect® Permanently Marked Controlled Duplex Receptacles

Description	Color	Standard		Tamper-Resistant	
		15A 125V	20A 125V	15A 125V	20A 125V
Duplex One Face Controlled Split Circuit Snap	White	SNAP5262C1W	SNAP5362C1W	SNAP5262C1WTRA	SNAP5362C1WTRA
Duplex Both faces Controlled	White	SNAP5262C2W	SNAP5362C2W	SNAP5262C2WTRA	SNAP5362C2WTRA
StyleLine Decorator One Face Controlled Split Circuit	White	SNAP2152C1W	SNAP2162C1W	SNAP2152C1WTRA	SNAP2162C1WTRA
StyleLine Decorator Both faces Controlled	White	SNAP2152C2W	SNAP2162C2W	SNAP2152C2WTRA	SNAP2162C2WTRA



SNAPConnect® Protection Receptacles

Description	Color	Hospital Grade		Specification Grade	
		15A 125V	20A 125V	15A 125V	20A 125V
Heavy Duty Commercial Ground Fault	White	SNAPGF82W	SNAPGF83W	GFRST15SNAPW	GFRST20SNAPW
Heavy Duty Commercial Ground Fault Tamper-Resistant Weather-Resistant	White	SNAPGFTW82W	SNAPGFTW83W	GFTWRST15SNAPW	GFTWRST20SNAPW
Surge Protection Tamper resistant with Power Indicating (LED)	White	SNAP8262WS	SNAP8362WS	SNAP5262WA	SNAP5362WS
USB Charger Duplex, one USB Type A and one Type-C port, 3 Amp up to 9 Volt USB output	White	SNAP8200UACW	SNAP8300UACW	SNAP15UACW	SNAP20UACW



SNAPConnect® Right Angle Pigtailed Connectors for Switches

Description	Solid		Stranded	
	15A 125V	20A 125V	15A 125V	20A 125V
6 inch wire connector for use with	single pole	SNAPSP1NA	SNAPSP2NA	
	single pole, with push-in terminals	SNAPSP1NAM2	SNAPSP2NAM2	
	single pole pilot light	SNAPSPP1NA	SNAPSPP2NA	
	single pole pilot light, with push-wire terminals	SNAPSPP1NAM2	SNAPSPP2NAM2	
	3-way pilot light	SNAP3W1NA	SNAP3W2NA	
	3-way pilot light, with push-wire terminals	SNAP3W1NAM2	SNAP3W2NAM2	



SNAPConnect® White Specification Grade Switches

Description	Style	15A, 120-277V AC		20A, 120-277V AC	
		Single Pole	Three Way	Single Pole	Three Way
Standard	Toggle Decorator	SNAP1201WNA SNAP2101WNA	SNAP1203WNA SNAP2103WNA	SNAP1221WNA SNAP2121WNA	SNAP1223WNA SNAP2123WNA
Illuminated blue LED, light ON with load OFF	Toggle Decorator	SNAP1201LWNA SNAP2101LWNA	SNAP1203LWNA SNAP2103LWNA	SNAP1221LWNA SNAP2121LWNA	SNAP1223LWNA SNAP2123LWNA
Pilot red LED, light ON with load OFF	Toggle Decorator	SNAP1201PLWNA SNAP2101PLWNA	—	SNAP1221PLWNA SNAP2121PLWNA	—



SNAPConnect® Testers

Description	Catalog Number
Circuit Tester for SNAPConnect® receptacle terminals, GFCI and standard receptacles	SNAPCTG
Switch jumper/tester, single pole, illuminated	SANPSWJUMP
Switch jumper/tester, 3-way, illuminated	SNAP3WJUMP



Polycarbonate Wallplates

Description	Standard		Mid-Size	
	1-Gang	2-Gang	1-Gang	2-Gang
StyleLine Decorator, white	P26W	P262W	PJ26W	PJ262W
Duplex, white	P8W	P82W	PJ8W	PJ82W
Toggle, white	P1W	P2W	PJ1W	PJ2W
Combination 1-Toggle and 1-Duplex, white	-	P18W	-	PJ18W
Combination 1-Duplex and 1-StyleLine Decorator, white	-	P826W	-	PJ826W
Combination 1-Toggle and 1-StyleLine Decorator, white	-	P126W	-	PJ126W



Dimensions in Inches (mm)