Straight Cuff Gloves Class 2 18" Yel/Blk Size 10H

By Chance Lineman Tools & Equipment
Catalog # PSC218YB10H

CLASS 2 18" YEL/BLK SIZE 10H

Features

- Class 2
- Maximum use voltage 17,000 volts AC / 25,500 DC
- color is yellow under black

General

Catalog Number	PSC218YB10H
Color	Yellow Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Straight Cuff
UPC	096359448884

Dimensions

Length	18 in
Weight	2.07 lb
Width	10.5 in

Electrical Ratings

Voltage - Maximum	• 17000 VAC • 25500 VDC
Voltage Rating	Class 2 V

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

Catalogs - Rubber Insulating Gloves
Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions
Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Spanish
Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions (07-1102-fra) French
Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Portuguese
Specifications - PSC218YB10H
Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field

©2024 Hubbell Incorporated. All rights reserved