


Features and Benefits

AV and Power Ceiling Boxes

The AV Ceiling Enclosure is designed to house active AV devices and integrate AV distribution, data connections and power in one location, providing a direct connection to a projector or a display device. The enclosure protects and conceals your equipment and connections for a clean installation while maintaining accessibility with the hinged access doors.

- Neatly Manage AV, power, and data requirements inside one enclosure
- Two Enclosures Sizes to Match your Required Application
- Flush mounted, white enclosure for consistent look when mounted in the ceiling
- Hinged access doors accepts field installed ceiling tiles
- Enclosures with 1-1/2" conduit hubs for projector mounting
- All steel rugged construction provides the ultimate strength for installation



HRCB12WHT



HRCB22PWHT

1' x 2' Plenum Rated Ceiling Boxes

Description	Length	Width	Height	Color	Catalog Number
Recessed ceiling box	23.69" (601.7mm)	11.69" (296.9mm)	6.00" (152.4mm)	White	HRCB12WHT
Recessed ceiling box with 1-1/2" NPT projector pole adapter	23.69" (601.7mm)	11.69" (296.9mm)	6.00" (152.4mm)	White	HRCB12PWHT
HRCB12 Series Box hard ceiling frame kit	23.57" (598.7mm)	12.94" (328.7mm)	7.38" (187.4mm)	White Flange	HRCB12HCFK
HRCB12 series box cooling fan kit	10.88" (276.3mm)	1.89" (48.1mm)	4.91" (124.6mm)		HRCB12FAN

Note: 1'x2' ceiling boxes includes; (1) external 15A, 125V single receptacle and internal (2) 15A, 125V leaded duplex receptacles.

2' x 2' Plenum Rated Ceiling Boxes

Description	Length	Width	Height	Color	Catalog Number
Recessed ceiling box	23.69" (601.7mm)	23.69" (601.7mm)	6.00" (152.4mm)	White	HRCB22WHT
Recessed ceiling box with 1-1/2" NPT projector pole adapter	23.69" (601.7mm)	23.69" (601.7mm)	6.00" (152.4mm)	White	HRCB22PWHT
HRCB22 Series Box hard ceiling frame kit	23.57" (598.7)	24.94" (633.5)	7.38" (187.4)	White Flange	HRCB22HCFK
HRCB22 series box cooling fan kit	9.54" (242.3mm)	1.89" (48.1mm)	4.89" (124.2)		HRCB22FAN

Note: 2'x2' ceiling boxes includes; (1) external switched 15A, 125V single receptacle and internal (5) 15A, 125V single receptacles

1' x 2' & 2' x 2" Ceiling Box Accessories

Description	Length	Width	Height	Size	Catalog Number
Ceiling box cable support kit, 4 cables	95" (2413.0mm)				HRCBMNT1
Ceiling box threaded rod kit, 4 brackets	0.88" (22.2)	0.06" (1.6mm)	1.19" (30.2)	0.09" (2.4mm) Dia Up to 3/8" Threaded Rod	HRCBTHRD

AV Ceiling Enclosure

- Manage multiple applications inside one enclosure
- Flush mounted, white enclosure for consistent look when mounted in the ceiling
- Loaded with two Hubbell 20A duplex receptacles and a 2-gang back box
- All steel rugged construction provides the ultimate strength for installation



AVCE1H

Dimensions in Inches (mm)

Description	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Color	Catalog Number
AV ceiling enclosure.	12" (305)	24" (610)	8" (203)	White	AVCE1H

Note: Enclosure includes two 20 amp duplex receptacles and 2-gang back box.