2″ Square Shaft Extension (SS200), 10ft

By CHANCE Foundation Solutions
Catalog # C1100566

SS200, 10′ (3048 mm) ft long with no helix

Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation
- Bolt and nut are assembled to extension at the factory

Application

Helical Anchoring

General

Catalog Number	C1100566
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	150000 lb.
Torque Rating	16000 ft-lbs
Type	Anchor Extensions
UPC	096359243298

Dimensions

Dimensions	120.00 in x 3.250 in x 5.000 in
Height	5 in
Length	120 in
Weight	147.412 lb
Width	3.25 in

Logistics

Pallet Quantity	12
Standard Package	1

Product Assets

Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure
Catalogs - CHANCE Civil Product Catalog
Catalogs - Anchors
Catalogs - CHANCE Instant Foundation Catalog
Installation Manuals - Chance Helical Pile/Anchor Installation Log Form to record installation details of Chance helical piles.
Literature - New Construction Helical Pile Foundation System
Literature - Square Shaft Efficient Helical Pile Design
Sales Drawings - SS200 Anchors
SDS - MSDS - Galvanized Steel Products
Specifications - C1100566
Video - CHANCE Square Shaft Anchor Installation
Video - CHANCE Square Shaft Anchor Tools Selection Process

©2024 Hubbell Incorporated. All rights reserved