

Universal Patch Panels and Wall Mount Brackets



Consolidation Point Block, Category 6 and Category 5e

Description	Catalog Number
Category 6, 12-Port, Universal, 89D.	HP612
Category 5e, 12-Port, Universal, 89D.	HP5E12

Universal Patch Panel, Category 5e

Description	Catalog Number
24-Port, 1.75" H.	HP5E24
48-Port, 3.50" H.	HP5E48
96-Port, 7.0" H.	HP5E96



HP5E24



HP5E48



NSPJ24



CMBR

Universal Patch Panel, Category 6

Description	Catalog Number
24-Port, 1.75" H.	HP624
48-Port, 3.50" H.	HP648
96-Port, 7.0" H.	HP696

Jack Panel, Unloaded

Description	Catalog Number
Wall Mount, 12-Port, Black.	HPJ1289
Rack Mount, 24-Port, 1.75" H, Black.	NSPJ24
Rack Mount, 48-Port, 3.5" H, Black.	NSPJ48

Rear Cable Management Bar*

Description	Catalog Number
Screws to the rear flange of a 19-inch rack.	CMBR
HPW panel mount.	HPRCMB

Note: *Not UL Listed.



HPWWB2U4



HPWWB4U8



HPWWB6U18



BRMCCMB19X7X4

Wall Mount Brackets, Bottom-Hinged

Includes assembled bottom-hinged wall bracket.

Rack Units	Width Inches (mm)	Depth Inches (mm)	Height Inches (mm)	Catalog Number
1	19" (483)	4" (102)	1.75" (45)	HPWWB1U4
2	19" (483)	4" (102)	3.50" (89)	HPWWB2U4
		8" (203)	3.50" (89)	HPWWB2U8
4	19" (483)	4" (102)	7.00" (178)	HPWWB4U4
		8" (203)	7.00" (178)	HPWWB4U8
6	19" (483)	4" (102)	10.50" (267)	HPWWB6U4
		8" (203)	10.50" (267)	HPWWB6U8
		18" (457)	10.50" (267)	HPWWB6U18

Wall Mount Brackets, Side-Hinged

Includes assembled side-hinged wall bracket.

Rack Units	Width Inches (mm)	Depth Inches (mm)	Height Inches (mm)	Catalog Number
2	19" (483)	4" (102)	3.50" (89)	BRMCCMB19X35X4
4	19" (483)	4" (102)	7.00" (178)	BRMCCMB19X7X4
2	19" (483)	8" (203)	3.50" (89)	BRMCCMB19X35X8
4	19" (483)	8" (203)	7.00" (178)	BRMCCMB19X7X8