Standard Underpinning Bracket

By CHANCE Foundation Solutions
Catalog # C1500299

Standard Underpinning Bracket (Std) fits SS175.

Features

- Finish: Galvanized
- Building Code Approved
- Bracket Only (includes hardware)

Application

Helical Anchoring

General

Coating	Galvanized
Finish Type	Galvanized
Shaft Type	SS
Strength Rating - Ultimate	40000 lb
Type	Underpinning
UPC	096359241430

Dimensions

Dimensions	16.00 in x 12.000 in x 6.000 in
Height	6 in
Length	16 in
Weight	36.3 lb
Width	12 in

Certifications And Compliance

ICC-ES Evaluated	ESR 2794
LARR Certified?	RR 25984

Logistics

Pallet Quantity	50

Product Assets

Catalogs - CHANCE Instant Foundation Catalog
Engineering Drawing - Standard Underpinning Bracket – 80 KIP
Installation Manuals - Underpinning Brackets C150-0121 and C150-0299 Installation Instructions
Literature - CHANCE® Building Code Evaluated Products December 2022
Sales Drawings - Standard Underpinning Bracket – 80 KIP
SDS - MSDS - Galvanized Steel Products
Test Documents - ICC Evaluation (NER2794)
Video - Hubbell Power Systems Helical Pile Shake Table Testing
Video - CHANCE® Square Shaft Installation
Video - Chance Foundation Solutions Anchor/Pile Installation Tools

©2024 Hubbell Incorporated. All rights reserved.
CN-C1500299-SPEC-EN | REV 6/2024