

New Innovations

Circuit-Lock® 30A Disconnects with LED Indicators

Hubbell's new 30A Circuit-Lock Disconnect with integral phase indication LEDs redefines the benchmark for safety by providing insight into the enclosure while in use. Six highly visible LEDs (3 line side/3 load side) communicate the electrical status of the switch by phase. This voltage detection feature significantly improves existing safety and maintenance procedures by visually providing personnel critical information prior to removing the enclosure cover; e.g. a welded contact or dropped phase.

Hubbell **inSIGHT™** phase indicating disconnect switches are available in non-metallic and stainless steel versions. Replacement covers are available for upgrades to existing installations. With an ever growing focus on safety improvements Hubbell **inSIGHT™** disconnects provide a difference you literally can see.

inSIGHT™

Insight (n): the power or act of seeing into a situation



Housing Design

- Six highly visible integral phase identification LEDs provide secondary means of visual confirmation of make/break on all phases
- Available in non-metallic, stainless steel and jog switch versions
- IP69k and Type 4X, 12K water ingress protection



Safety

- High visibility red handle can be locked in the OFF position to comply with OSHA Lockout/Tagout requirements
- Quickly upgrade the safety of existing installations with an **inSIGHT™** replacement cover
- Verification of opening of load side contacts



Unfused Disconnect Switches with LEDs

Description	30 Amp	60 Amp	100 Amp
Non-Metallic disconnect switch with LEDs	HBLDS3P	HBLDS6P	HBLDS10P
Non-Metallic disconnect switch with HBLAC1 auxiliary contact	HBLDS3PAC	HBLDS6PAC	HBLDS10PAC
Stainless Steel square top disconnect switch with LEDs	HBLDS3SSP	HBLDS6SSP	HBLDS10SSP
Stainless Steel square top disconnect switch with HBLAC1 auxiliary contact	—	HBLDS6SSPAC	HBLDS10SSPAC
Stainless Steel sloped top disconnect switch with LEDs	HBLDS3SSRP	HBLDS6SSRP	HBLDS10SSRP
Stainless Steel sloped top disconnect switch with HBLAC1 auxiliary contact	—	HBLDS6SSRPAC	HBLDS10SSRPAC

Note: *Certified by NSF, International.
For use with 3Ø Y configurations only.

Auxiliary Contacts

Description	Catalog Number
"Break After Main Break", 1 set of n/o contacts, 1 set of n/c contacts.	HBLAC1**
"Break Before Main Break", 1 set of n/o contacts for use with variable frequency drives.	HBLAC2**



HBLDS3P



HBLDS3SSRP