







GFCI, USB, Surge Receptacles and Style Line® Device Wallplates

Description	Color	Thermoplastic			Material	Metal Catalog Number
		Standard	Mid-Size	Jumbo		
1-Gang, 1-Decorator 	Black	P26BK	PJ26BK	-	Aluminum	①
	Blue	-	PJ26BL	-	Brass	SB26
	Brown	P26	PJ26	-	Brass Plated	SBP26
	Gray	P26GY	PJ26GY	-	Chrome	SCH26
	Ivory	P26I	PJ26I	NPJJ26I	S/S 302/304	SS26
	Light Almond	P26LA	PJ26LA	NPJJ26LA	S/S 430	SS26L
	Red	P26R	PJ26R	-		
	White	P26W	PJ26W	NPJJ26W		
2-Gang, 2-Decorator 	Black	P262BK	PJ262BK	-	Aluminum	①
	Brown	P262	PJ262	-	Brass	SB262
	Gray	P262GY	PJ262GY	-	Brass Plated	SBP262
	Ivory	P262I	PJ262I	-	Chrome	SCH262
	Light Almond	P262LA	PJ262LA	-	S/S 302/304	SS262
	Red	P262R	PJ262R	-	S/S 430	SS262L
	White	P262W	PJ262W	-		
3-Gang, 3-Decorator 	Black	P263BK	PJ263BK	-	Aluminum	①
	Brown	P263	PJ263	-	Brass	①
	Gray	P263GY	PJ263GY	-	Brass Plated	SBP263
	Ivory	P263I	PJ263I	-	Chrome	①
	Light Almond	P263LA	PJ263LA	-	S/S 302/304	SS263
	Red	P263R	-	-		
	White	P263W	PJ263W	-		
4-Gang, 4-Decorator 	Black	P264BK	-	-	Aluminum	①
	Brown	P264	-	-	Brass	①
	Gray	P264GY	-	-	Brass Plated	①
	Ivory	P264I	PJ264I	-	Chrome	①
	Light Almond	P264LA	PJ264LA	-	S/S 302/304	SS264
	White	P264W	PJ264W	-		
5-Gang, 5-Decorator 	Gray	P265GY	-	-	Aluminum	①
	Ivory	P265I	-	-	Brass	①
	Light Almond	P265LA	-	-	Brass Plated	①
	White	P265W	-	-	Chrome	①
					S/S 302/304	SS265
6-Gang, 6-Decorator 	Black	P266BK	-	-	Aluminum	①
	Brown	P266	-	-	Brass	①
	Gray	P266GY	-	-	Brass Plated	①
	Ivory	P266I	-	-	Chrome	①
	Light Almond	P266LA	-	-	S/S 302/304	SS266
	White	P266W	-	-		

Note: Thermoplastic wallplates feature pre-inserted captive screws for faster assembly in single gang configurations.

① Available as a custom wallplate, see pages O-32 to O-34. Consult custom wallplates section for additional openings and combinations.

Dimensions in Inches (mm)