




Plates for Use in SystemOne 2, 4 and 6-Gang Floor Boxes

- UL 514A listed

Cat. No.	Plate Style	Cat. No.	Plate Style
FB10MPREC	(1) Decorater Opening	FB10MPDUP	(1) Duplex Opening
FB10MPBNK	1-Gang Blank Plate	FB10MPKEY	(1) Opening with Hubbell 6-Port Frame for Keystone Jacks Frame for Keystone Jacks
FB10MPTRAC	(2) Openings for (6) Ortronics TracJacke®	FB10MPFT	Cable Feed Through with Bushing
Cat. No	Two Gang Plate Style	Cat. No	Two Gang Plate Style
FB10MP2A	Decorater Openings	FB10MP2E	Duplex Openings
FB10TLX	(1) Simplex Opening 1.40 in. Diameter	FB10TLA	(1) Twist-Lock® Opening 1.60 in. Diameter
FB10MP2B	(6) 1U Hubbell iStation Modules	FB10MPMAAP	Siemon CT Series
FB10MPAAP	(4) Extron® AAP Openings		
Cat. No	Three Gang Plate Style	Cat. No	Three Gang Plate Style
FB10TLY	(2) Simplex Opening 1.40 in. Diameter	FB10TLB	(3) Twist-Lock® Opening 1.60 in. Diameter
FB10MP3GAPP	(1) Opening for Appliance Receptacle, requires 2-Gang industry plate for trim out		
Cat. No	Five Gang Plate Style	Cat. No	Five Gang Plate Style
FB10TLC	(3) Simplex Opening 1.40 in. Diameter	FB10TLZ	Twist-Lock® Opening 1.60 in. Diameter
FB10MPNEMA2XG	(2) 2-Gang. Meets NEMA Spacing. Ideal for Crestron® DM –TX Product and Power. Ships with Low Voltage Divider.	FB10MPNEMA4G	(4) Single Service Openings Utilizing NEMA Wallplate. (No Low Voltage Divider Option)



Note: *Use with FB10MPNEMA2XG and/or FB10MPNEMA4G for 8-gang configuration.



Pre-Wired Device Plates

- Reduces wiring and installation times
- 8 inch stranded leads mounted to the face plate

Description	Type	15A	20A
Duplex, Gray.	Standard Tamper-Resistant	PWFB10MPCR15GRY PWFB10MPCR15GRYTR	PWFB10MPCR20GRY PWFB10MPCR20GRYTR
Decorater, Gray.	Standard Tamper-Resistant	PWFB10MPDR15GRY PWFB10MPDR15GRYTR	PWFB10MPDR20GRY PWFB10MPDR20GRYTR



Accessories

Description	Catalog Number
(1) 2" threaded zinc hub for use with CFB2G30, CFB4G30 and CFB6G30 series floor boxes; replaces CFBKOPLATE.	CFBHUB2
(2) 1-1/4" PVC hubs with reducers for use with CFB2G30, CFB4G30 and CFB6G30 series floor boxes; replaces CFBKOPLATE. Reducers include: (2) 1" reducer, (2) 3/4" reducers, and (2) 1/2" Reducer/Plugs.	CFBHUB125PVC
(2) 2" PVC hubs with reducers for use with CFB2G30, CFB4G30 and CFB6G30 series floor boxes; replaces CFBKOPLATE. Reducers include: (2) 1-1/2" reducers, (2) 1-1/4" reducers, and (2) 1" Reducer/Plugs.	CFBHU200PVC
Replacement knock-out plates.	Standard Epoxy Coating CFBKOLATE CFBKOPLATECR
Replacement Round Cover Adapter, 10-gang Floor Box	CFB10GS1R8ADAPT
Stackable ring to increase box height and concrete pour depth by 3/4 in. increments above top plane of floor box. One ring per 3/4 in. depth increase. Must be installed before concrete pour.	CFB8RCVRR75
Finished floor height adjustment ring - increase post pour adjustment ; use with round cover series.	0 - 1/4 in. 1/4 in. - 1/2 in. 1/2 in. - 3/4 in. CFB8RCVRR1* CFB8RCVRR2 CFB8RCVRR3
Rectangular pre-pour 1/2 in. extension caps (2 pack).	610GEXTENDCAP2PK
Replacement temporary concrete pre-pour covers	610GTEMPCVR
Replacement spacer around wire-way.	FB10MPX
Replacement divider.	FB10GDIV



Note: *Included with standard CFB10G55R series floor boxes.

Extron® is a registered trademark of Extron Electronics. Crestron® is a registered trademark of Crestron Electronics, Inc. FSR® is a registered trademark of FSR Inc. TracJack®, Series II® and Ortronics® are registered trademarks of Ortronics/Legrand.

Dimensions in Inches (mm)