HUBBELL
Industrial Controls

HC4292001303 TYPE 4292 MAG SIZE 2 CTRL 12VDC YEL ENCL

By Hubbell Industrial Controls (ICD)
Catalog # HC4292001303

TYPE 4292P YARDMASTER PUP, LIFTING MAGNET CONTROLLER, AUTOMATIC DISCHARGE VARISTOR, 5-50 AMPS COLD MAGNET CURRENT, 12 VOLTS DC CONTROL CIRCUIT, NEMA 3R ENCLOSED

Features

- Automatic Discharge. Rated 5-50 amps DC. Front-Wired, Front-Removable components.
- Mechanically interlocked “Lift” and “Drop”. NEMA rated mill duty contactors.
- Permanently connected 700V discharge path completely independent from the line that protects magnet and generator.
- High-Thermal capacity varistor discharge path.
- Peak magnet induced voltage limited to under 700 volts.
- Long electrical contact life. Minimum maintenance.
- Dribble control standard on 115V & 230V controllers.
- Ventilated Indoor/Outdoor NEMA 3R Enclosure.
- 5 to 100 Amps cold magnet current.
- Heavy-duty time proven components arranged to provide optimum control of your lifting magnets.
- Mechanically interlocked “Lift” and “Drop” NEMA rated mill duty contactors.

General

Catalog Number	HC4292001303
Series	4292P Yardmaster Pup
Type	Automatic Discharge

Dimensions

Dimensions	19 in x 14 in x 34.25 in
Height	34.25 in
Length	19 in
Width	14 in

Electrical Ratings

Current / Amperage Rating	5-50 A

Certifications And Compliance

Contactor NEMA Rating	2
Enclosure NEMA Rating	3R

Product Assets

Catalogs - 100E Euclid Brochure
Catalogs - 4292P Yardmaster Pup Lifting Magnet Controller Catalog
Installation Manuals - ICD_4292PPub207_CATALOG
Specifications - HC4292001303

©2024 Hubbell Incorporated. All rights reserved