Wallplate Frames, Delivery Bezels, Modules and Gangable AV Wallboxes







c(UL)us

Hubbell iSTATION Modular Wallplate Frames

Single-service,	low voltage				
Color	1-Gang	2-Gang	3-Gang	4-Gang	
Black	IMF1BK	IMF2BK	IMF3BK	IMF4BK	
Gray	IMF1GY	IMF2GY	IMF3GY	IMF4GY	
lvory	IMF1EI	IMF2EI	IMF3EI	IMF4EI	
Office White	IMF1OW	IMF2OW	IMF3OW	IMF4OW	
White	IMF1W	IMF2W	IMF3W	IMF4W	
Multi-service, p	ower and low voltage				
Color	1-Gang Decorator 1-Gang iSTATION	2-Gang Decorator	1-Gang Decorator 2-Gang iSTATION	1-Gang Decorator 3-Gang iSTATION	2-Gang Decorator 2-Gang iSTATION
Black	IMFP1D1BK	IMFP2BK	IMFP1D2BK	IMFP1D3BK	IMFP2D2BK
Gray	IMFP1D1GY	IMFP2GY	IMFP1D2GY	IMFP1D3GY	IMFP2D2GY
lvory	IMFP1D1EI	IMFP2EI	IMFP1D2EI	IMFP1D3EI	IMFP2D2EI
Office White	IMFP1D1OW	IMFP2OW	IMFP1D2OW	IMFP1D3OW	IMFP2D2OW
White	IMFP1D1W	IMFP2W	IMFP1D2W	IMFP1D3W	IMFP2D2W

Hubbell iSTATION Stainless Steel Plates

1-Gang	2-Gang	3-Gang	4-Gang	
1111331	1111332	1111333	111334	

Delivery Bezels and Modules

		Hubbell iSTATION Bezel	
Color	Raceway Bezel	for Third-Party Raceway	Furniture Boxes
Black	-	-	HBLIMFBK
Gray	KPIMBZGY	HWAPLGY	HBLIMFGY
lvory	-	-	HBLIMFI
Office White	KPIMBZOW	HWAPLOW	-
White	-	HWAPLW	HBLIMFWA



Third-Party Raceway Modules

Unloaded, 2-port, 10-pack			
Color	Catalog Number		
Black	HWM2KBK10		
Gray	HWM2KGY10		
lvory*	HWM2KI10		
White	HWM2KW10		

Note: *Equivalent to Hubbell Office White.

Two and Three Gangable AV Wallboxes

	<u> </u>				
Box	Dimensions	Top Knockouts	Bottom Knockouts	Back Knockouts	Catalog Number
2-Gang, 2" KO, 54in ³ capacity	H: 4.21" W: 4.06" D: 4.0"	(2) ½" (2) ½" – ¾" TKO*	(1) 1", 1¼", 1½" & 2"	(2) ½" – ¾" TKO	HBL985
3-Gang, 2" KO, 79in ³ capacity	H: 4.21" W: 5.87" D: 4.0"	(3) ½" (3) ½" – ¾" TKO*	(1) ½" (1) ½" – ¾" TKO* (1) 1", 1¼", 1½" & 2"	(3) ½" – ¾" TKO	HBL986

Note: *TKO (Tangential Knockout).

Low Voltage AV Wallbox Partitions

Compatible With	Description	Quantity	Catalog Number
HBL985 and HBL986	Solid divider	1	HBL989
	With pass-thru capability	1	HBL989AVD

