

IMPORTANT SAFETY INFORMATION. READ AND FOLLOW ALL SAFETY INSTRUCTIONS. Follow label information and instructions concerning Wet or Damp Locations, installation near combustible materials, insulation, building materials, and proper lamping. Do not install in areas subject to combustible vapors or gases. Before wiring to power supply and during servicing or relamping, turn off power at fuse or circuit breaker. All servicing or relamping must be performed by qualified service personnel. Product must be grounded to avoid potential electric shock or other potential hazard. Product must be mounted in locations and at heights and in a manner consistent with its intended use, and in compliance with the National Electrical Code and local codes. The use of accessory equipment not recommended by the manufacturer or installed contrary to instructions may cause an unsafe condition. Do not block light emanating from product in whole or part, as this may cause an unsafe condition. Do not allow items such as drapes, curtains, screens or the like to come into contact with the product or to block light from the product, as this may cause an unsafe condition.

# INSTALLATION INSTRUCTIONS

## ARCHITRAK® SYSTEM

### INSTALLATION INSTRUCTIONS

FOR FIELD CUTTING TRACK TO SPECIAL LENGTHS.

FOR USE WITH PRESCOLITE AKT TRACK SYSTEM ONLY

READ INSTALLATION INSTRUCTIONS BEFORE INSTALLING TRACK SYSTEM.

SAVE INSTRUCTIONS FOR REFERENCE WHEN MAKING ADDITIONS TO OR CHANGES IN THE TRACK SYSTEM.

### INSTALLATION

1. Refer to PRECOLITE AKT series track for track installation instructions.
2. Remove live end feed and track end cap before cutting track. Track can be cut anywhere along its length. Cut must be at 90° degrees to track rail.
3. Cut track to required length with hacksaw or any other suitable cutting tool.
4. Remove all burrs from insulators, track and copper buss bars. Reinstall track end cap and appropriate feed connectors, tighten retaining screws.
5. **CAUTION:** After track has been cut make certain each section of track 4 feet or less has one mounting hole a maximum of 6 inches from each end. A section of track greater than 4 feet in length must have a mounting hole a maximum of 12 inches from each end. Additional mounting holes may be provided as required.

### TO ADDITIONAL MOUNTING HOLES, FOLLOW THIS PROCEDURE.

1. Locate mounting holes along center line of track. Center line is the v groove on the inside of track rail.
2. Drill hole using 1 1/4" inch drill bit.
3. **CAUTION:** Take care you do not damage buss bar insulators during the drilling operation. If you accidentally damage any insulators. Discard the track section. DO NOT USE A DAMAGED TRACK SECTION IN THE INSTALLATION.
4. Remove all burrs from drilled holes.

