


Area/Site Accessories

Square Steel Pole Mounting Brackets

The ARM brackets are made from 2 3/8" OD steel tubing and are designed to mount on square steel poles (SSS Series). Units are offered in gray or dark bronze powder paint finishes to match our ASL luminaires. Brackets are the #2 drilling pattern on Hubbell / Spaulding poles. Mounting hardware for those poles is included.

MADE-TO-ORDER

Catalog Number	Length (Inches)	OD	Finish	EPA	Weight lbs (kg)	PKG. CODE
ARM-F-M12-BL	12"	2 3/8"	Black	-	7 (3.2)	BC
ARM-F-M12-DB	12"	2 3/8"	Bronze	-	7 (3.2)	BC
ARM-F-M12-GR	12"	2 3/8"	Gray	-	7 (3.2)	BC
ARM-F-M12-PS	12"	2 3/8"	Platinum	-	7 (3.2)	BC
ARM-F-M12-WH	12"	2 3/8"	White	-	7 (3.2)	BC



ARM - F - M12 - XX

Area/Site Accessories

MADE-TO-ORDER


CIMARRON CL1 ACCESSORIES (ORDER SEPARATELY)

CR-RPAX-XX MAF



Catalog Number	Description
CR-RPA3-XX ¹	Round pole adapter for straight arm (3 1/4" - 3 3/4")
CR-RPA4-XX ¹	Round pole adapter for straight arm (3/8" - 4 1/2")
CR-RPA5-XX ¹	Round pole adapter for straight arm (5")
CR-RPA6-XX ¹	Round pole adapter for straight arm (6")
CRD-RPA2-XX ¹	Round pole adapter for upswept arm (2 3/4" - 3 1/8")
CRD-RPA3-XX ¹	Round pole adapter for upswept arm (3 1/4" - 3 3/4")
CRD-RPA4-XX ¹	Round pole adapter for upswept arm (3/8" - 4 1/2")
CRD-RPA5-XX ¹	Round pole adapter for upswept arm (5")
CRD-RPA6-XX ¹	Round pole adapter for upswept arm (6")
WB-CR-XX ¹	Wall bracket
TPLB-XX ¹	Twin parallel luminaire bracket
MAF-CL-XX ²	Horizontal mast arm fitter for 2 3/8" OD arm. Mounts to standard 6" arm (ordered with fixture)

CIMARRON LED CL1 FIXTURE MOUNTING - SQUARE & ROUND



UPSWEPT ARM MOUNT
SQUARE & ROUND POLES

MADE-TO-ORDER

ADJUSTABLE MOUNTING ARMS



ARM-CL-K-S-XX

Adjusts in 4° increments




ARM-CL-TK-TA-XX



Adjusts in 4° increments

Catalog Number	Description	EPA ft ² (m ²)	Weight lbs. (kg)
ARM-CL-K-TA-XX ¹	2 3/8" OD tenon slipfitter for single fixture	—	5 (2.3)
ARM-CL-TK-TA-XX ¹	2 3/8" OD tenon slipfitter for twin fixture (180°)	—	7 (3.2)
ARM-CL-K-S-XX ¹	10" Adjustable arm	0.5 (0.05)	5.75 (2.6)

Replace XX with color designation: **DB** - Dark Bronze, **BL** - Black, **WH** - White, **GR** - Gray, **PS** - Platinum Silver, **RD** - Red (Premium Color), **FG** - Forest Green (Premium Color), **CC** - Custom Color (consult factory)



MAF - HORIZONTAL MAST ARM FITTER
(CL1 ONLY)




#2 DRILL PATTERN FOR POLES
(CL1 AND CL15)

MADE-TO-ORDER

TOP POLE BRACKET ACCESSORIES CL1 AND CL15 (ORDER SEPARATELY)

Catalog Number	Description	EPA ft ² (m ²)	Weight lbs. (kg)
SETA 2-XX ¹	4" Square pole top tenon adapter 2 3/8" OD slipfitter for max. four fixtures (90°)	0.4 ft ² (.04 m ²)	20 lbs. 9 kgs.
RETA 2-XX ¹	4" Round pole top tenon adapter 2 3/8" OD slipfitter for max. four fixtures (90°)	0.2 ft ² (.02 m ²)	20 lbs. 9 kgs.
TETA 2-XX ¹	Three sided pole top tenon adapter 2 3/8" OD slipfitter for max. four fixtures (120°)	0.2 ft ² (.02 m ²)	20 lbs. 9 kgs.



CIMARRON CL15 ACCESSORIES (ORDER SEPARATELY)


CL15-RPAX-XX



Catalog Number	Description
CL15-RPA3AAC-XX ¹	Round pole adapter for straight arm (3 1/4" - 3 3/4")
CL15-RPA4AAC-XX ¹	Round pole adapter for straight arm (3/8" - 5")
WB-CR-XX ¹	Wall bracket

1 Replace XX with color choice, eg.: **DB** for Dark Bronze

CIMARRON LED CL15 FIXTURE MOUNTING - SQUARE & ROUND



MADE-TO-ORDER

FUNCTIONAL ACCESSORIES (ORDER SEPARATELY)

Catalog Number	Description
PTL-1	Photocontrol - twist-lock cell (120V)
PTL-8	Photocontrol - twist-lock cell (120-277V)
PTL-5	Photocontrol - twist-lock cell (480V)
PTL-6	Photocontrol - twist-lock cell (347V)
PSC	Shorting cap - twist-lock

MADE-TO-ORDER

MOUNTING ACCESSORIES (ORDER SEPARATELY)

Catalog Number	Description
RPA Round Pole adapters are available for 2, 3, 4.5, 5, and 6 inch diameter round poles	
RPA2-ARA3-XX ¹	Round Pole adapters for 2-1/2" - 3" diameter mounting surface
RPA3-ARA3-XX ¹	Round Pole adapters for 3" - 3-3/4" diameter mounting surface
RPA4-ARA3-XX ¹	Round Pole adapters for 3-7/8" - 4-1/2" diameter mounting surface
RPA5-ARA3-XX ¹	Round Pole adapters for 5" - 6" diameter mounting surface
RPA6-ARA3-XX ¹	Round Pole adapters for 6" diameter mounting surface

1 Replace XX with color choice, eg.: **DB** for Dark Bronze

