

# Boxes & Covers

ACCESSORIES

Hubbell has a variety of junction boxes and covers to allow easy installation of lampholders, compact floodlights and landscape luminaires. Cast aluminum construction, gasketed covers designed for

wet locations and conduit plugs are standard. Boxes have a natural aluminum finish. Covers are painted gray or black.

### ORDERING INFORMATION: Cast Round Boxes



Catalog Number	Size in. (mm)	Hubs						Mt. Lugs	Weight lbs. (kg)	PKG. CODE	Source
		Side		Back		Cover					
		Qty.	Size	Qty.	Size	Qty.	Size				
S-329-B	4 (102)	4	1/2"	1	1/2"	1	1/2"	2	.75 (0.3)	BC	STOCK

### MADE-TO-ORDER ORDERING INFORMATION: Specialty Boxes (All Hubs Tapped NPSM)

Catalog Number	Description	Weight lbs. (kg)	PKG. CODE
C-5	Wall or tree box: 3 mounting lugs in body; 2 1/2" hubs in "L" shape layout - side access plate	.25 (.11)	BC

### ORDERING INFORMATION: Round Covers - Cast Aluminum With Hubs

Catalog Number	Size in. (mm)	Boxes Used With	Tapped Hubs		Finish	Weight lbs. (kg)	PKG. CODE	Source
			Qty.	Size				
206-BC3	4 (102)	3 1/4" x 4" (83 mm x 102 mm)	3	1/2"	Gray	.5 (0.2)	BC	STOCK
206-BC3-B	4 (102)	3 1/4" x 4" (83 mm x 102 mm)	3	1/2"	Black	.5 (0.2)	BC	MADE-TO-ORDER



C-5



206-BC3

# Landscape Accessories

- These accessories make it simple to install the various Lightscaper® fixtures
- Two grades of burial junction boxes, portable spike mounts and 2 3/8" stub up fitters are specifically designed to mate with lampholders and louver lights


**STOCK**

### ORDERING INFORMATION: Landscape Accessories


Catalog Number	Description	Weight lbs. (kg)	PKG. CODE
<b>Fitter</b>			
S-302	Slipfits 1 1/2" or 2" pipe (1.9" OD or 2 3/8" OD) with 1/2" N.P.S.M. hub; Gray	.6 (0.3)	BC
S-302-M51	Slipfits 1 1/2" or 2" pipe (1.9" OD or 2 3/8" OD) with 1/2" N.P.S.M. hub; Bronze	.6 (0.3)	BC
TRN-XX	Trunnion adaptor for 1/2" threaded knuckle mount	.6 (0.3)	BC

### MADE-TO-ORDER ORDERING INFORMATION: Landscape Accessories


Catalog Number	Description	Weight lbs. (kg)	PKG. CODE
<b>Junction Boxes</b>			
NM-BC	Non-metallic high impact phenolic weatherproof box and cover; Box is drilled at 180° for two burial cable connectors, included, allowing feed-through capability; Gasketed cover has weathertight 1/2" hub; Brass cover screws; Gray	—	BC
1414-BOX	Cast Iron Box - 2 side hubs, one top (1/2"); Heavy Duty; Gray	5 (2.3)	BC
<b>Ground Spikes</b>			
1031-3	Cast spike with internal splice box, 1/2" N.P.S.M. hub for fixture and 6' #18/3 grounded cord set; Gray	1.75 (0.8)	BC
<b>Fitters</b>			
S-302-M52	Slipfits 1 1/2" or 2" pipe (1.9" OD or 2 3/8" OD) with 1/2" N.P.S.M. hub; White	.6 (0.3)	BC



NM-BC



1414-BOX



1031-3



S-302



TRN-XX



**HUBBELL**  
Outdoor Lighting