






# Photocontrols



## STOCK ORDERING INFORMATION

Catalog Number	Voltage	Max. Watts Incand.	Max. Watts HID		Weight lbs. (kg)	PKG. CODE
			HPF	NPF		
<b>Photocontrol - Button Type<sup>1</sup></b>						
 PBT-1 <sup>6</sup>	120	1200	400	250	.125 (0.1)	SCC
PBT-234 <sup>6</sup>	208/240/277	1200	400	250	.125 (0.1)	SCC

## MADE-TO-ORDER ORDERING INFORMATION

Catalog Number	Voltage	Max. Watts Incand.	Max. Watts HID		Weight lbs. (kg)	PKG. CODE
			HPF	NPF		
<b>Photocontrol - 1/2" Thread Mount<sup>2</sup></b>						
 PTA-1 <sup>6</sup>	120	2000	1000	400	.25 (0.1)	SCC
PTA-8 <sup>6</sup>	120-277	2000	1000	400	.25 (0.1)	SCC
PTA-5 <sup>6</sup>	480	2000	1000	400	.25 (0.1)	SCC
<b>Photocontrol - Twist-Lock<sup>®</sup> Cell<sup>3</sup></b>						
 PTL-1 <sup>6</sup>	120	1800	1000	400	.25 (0.1)	SCC
PTL-8 <sup>6</sup>	120-277	1800	1000	400	.25 (0.1)	SCC
PTL-5	480	1800	1000	400	.25 (0.1)	SCC
PTL-6 <sup>6</sup>	347	1800	1000	400	.25 (0.1)	SCC
<b>Receptacle - Remote Twist-Lock<sup>®</sup> Cell with Bracket<sup>4</sup></b>						
 PRR	120-480	1800	1000	400	.5 (0.2)	SCC
<b>Shorting Cap - Twist-Lock<sup>®</sup> Mount<sup>5</sup></b>						
 PSC	Completes circuit - Eliminates PCR				.25 (0.1)	SCC

- 1 Miniature photocontrol sealed in a sturdy plastic housing 2 1/16" x 1 1/8" x 7/8" with 3/4" nipple length, nipple dia. is 3/8" pipe thread - 5/8" outside diameter fits 1/2" tapped hubs; Use in any suitable enclosed box or luminaire; A gasket and lock nut provide weather tight seal at exit point
- 2 Weatherproof photocontrol in a polycarbonate housing with field adjustable light sensitivity level feature; 3 5/8" x 2" x 1 1/2" housing with 5/8" nipple length
- 3 Weatherproof Twist-Lock<sup>®</sup> photocell enclosed in a high butyrate protective housing; Meets EEL-NEMA standards; For use with Twist-Lock<sup>®</sup> receptacles (PCR)
- 4 Remote receptacle for PTL Twist-Lock<sup>®</sup> cell; Includes aluminum angle bracket and color coded leads; Bolts to wood poles, crossarms, walls or any flat surface
- 5 Weatherproof shorting cap to complete circuit and allow fixture to operate when Twist-Lock<sup>®</sup> photocontrol (PTL) is not used; For use with Twist-Lock<sup>®</sup> receptacles (PCR)
- 6 CSA certified