KILLARK®

EQF3230B2G - 32W Fluorescent 120-277V 3/4" Wall Mount with Guard

By Killark
Catalog # EQF3230B2G

32W Fluorescent 120-277V 3/4" Wall Mount with Guard.

Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25˚ stanchion or 90˚ wall mount, all with "wireless" design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction. Baked powder epoxy finish, electrostatically applied. Exposed hardware is 316 grade stainless steel.

General

Catalog Number	EQF3230B2G
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Lamp Type	Quad Pin
Light Source	
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Optic Type	Glass Globe - Clear
Series	EQF
UPC	783936143484

Dimensions

Hub Size	3/4"

Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	120-277 VAC
Wattage	32 W

Certifications And Compliance

Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D Class I, Zones 1 & 2, Groups IIB, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2

Product Assets

Customer Notices - Prop 65 Notice
Photometry - KIL_EQF32x-A
Photometry - KIL_EQF32x-S
Photometry - KIL_EQF32x

A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved