

GENERAL NOTES: (READ SHEETS COMPLETELY BEFORE STARTING)


1. LEAVE PROTECTIVE WRAPPING ON FIXTURE UNTIL START OF INSTALLATION.
2. FIXTURES ARE PROVIDED WITH FACTORY-INSTALLED BRANCH CIRCUIT WIRING. REFER TO SUPPLEMENTAL INSTRUCTION SHEET WHEN MAKING CONNECTIONS.
3. FIXTURES ARE MOUNTED ON DRYWALL CEILING SUPPORTED BY (2) 1/4-20 THREADED RODS SUPPLIED BY INSTALLER.
4. APPROXIMATE WEIGHT OF FIXTURE IS 3.50 LBS PER FOOT OF LENGTH.

TOOLS REQUIRED


- SCREWDRIVER/DRILL
- 11/32" NUT DRIVER

SUPPLIED BY INSTALLER


- THREADED RODS




AT CORRECT LOCATIONS IN CEILING, INSTALL (2) 1/4-20 THREADED RODS PER FIXTURE. SEE PLAN VIEW ON PAGE 1. THREADED RODS MUST END 3.50" ABOVE FINISHED CEILING.




DETACH LED REFLECTOR ASSEMBLY FROM FIXTURE BY REMOVING 1/4 TURN FASTENERS. SHIFT FASTENERS OUT AND LET REFLECTOR HANG DOWN ON NYLON TETHERS.




MOUNT END CAP ASSEMBLY (SHIPPED SEPARATELY) TO NEAR END OF 1ST FIXTURE USING TWO (2) #8 SHEETMETAL SCREWS. IF INSTALLING INDIVIDUAL FIXTURE, REPEAT AT FAR END. IF INSTALLING ROW, REPEAT AT FAR END OF LAST FIXTURE.



REMOVE (1) 7/8" KNOCK-OUT FROM TOP OF HOUSING AT DESIRED FEED LOCATION.
REMOVE BOTH 5/8" KNOCK-OUTS AT ENDS OF HOUSING FOR THREADED ROD ATTACHMENT. IF INSTALLING ROW, REPEAT FOR ALL FIXTURES.




LIFT FIRST FIXTURE UP NEAR CEILING OPENING AND BRING ELECTRICAL FEED INTO FIXTURE WIREWAY. RAISE FIXTURE UP FLUSH TO CEILING OPENING AND SECURE TO (2) THREADED RODS WITH FENDER WASHERS AND FLANGE NUTS FOUND IN POLYBAG.




RAISE AND SECURE NEXT FIXTURE IN ROW PER STEP 4. LOOSELY BOLT FIXTURES TOGETHER AT JOINT. FOR 3L, USE (2) #8 SHEET METAL SCREWS. FOR 4L AND 6L, USE (2) 8-32 X 3/8" LONG MACHINE SCREWS AND NUTS. LEVEL AND ALIGN FIXTURES BEFORE TIGHTENING FASTENERS. REPEAT FOR ADDITIONAL FIXTURE(S) IN ROW.

7




MAKE ALL WIRING CONNECTIONS. FOR ROW, BRANCH CIRCUIT WIRES CAN BE ROUTED THROUGH 7/8" FEED HOLES AT FIXTURE JOINTS.

8



REATTACH ALL LED REFLECTOR MODULE ASSEMBLIES. FOR ROW, ATTACH ROW JOINT COVERS (SHIPPED SEPARATELY) BY SNAPPING THEM INTO ADJACENT LED REFLECTORS. CLEAN FIXTURE EXTERIORS USING GENERAL WINDOW CLEANER.

9



PULL LENS GAP COVER DOWNWARD INTO THE POSITION SHOWN. SNAP DIFFUSER INTO BOTTOM OF FIXTURE HOUSING AND PUSH LENS GAP COVER BACK UP. TO REMOVE DIFFUSER, PULL LENS GAP COVER DOWN, THEN INSERT SCREWDRIVER OR FLAT HEAD PRY TOOL INTO SIDE OF HOUSING AND PULL DOWN.

NOTE:
LAST DIFFUSER IN ROW MUST BE CUT TO LENGTH PER INSTRUCTION SHEET 510647.