HUBBELL
Premise Wiring

Copper Solutions, Cable, NEXTSPEED, 10GBE, Riser Rated, Spool, Orange

By Hubbell Premise Wiring
Catalog # C6ASROR

Copper Solutions, Cable, NEXTSPEED, 10GBE, Riser Rated, Spool, Orange

Features

- NEXTSPEED
- 10GBE
- Riser Rated
- Spool
- Orange

Application

Riser

General

Catalog Number	C6ASROR
Construction	Copper/Insulation Eccentricity Shall Be 90% Minimum
Data Transfer Rate	10GbE
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6A UTP Cable
Material - Jacket	PVC
OEM Brand Name	Hubbell Premise Wiring
Temperature Rating	-20oC to +50oC (-4oF to +122oF)
UPC	662620288093

Electrical Ratings

Capacitance	5.6 nF/100 Meters @ 1 kHz
Impedance	100

Conductor Related

Conductor Size	#23 AWG
Conductor Type	Solid Bare Copper
Nema Color	Orange
Pairs Or Conductor	4-Pair

Logistics

Carton Quantity	1000

Product Assets

Catalog Page - PREM E4 CatalogPage
Catalogs - Premise Wiring Catalog
Literature - Catch the Wi-Fi 6 Wave
Specifications - C6ASROR

©2024 Hubbell Incorporated. All rights reserved