HUBBELL
Premise Wiring

7-Gang CFB Series Box for Rectangular Covers, 4.08" Minumum Depth of Pour

By Hubbell Premise Wiring
Catalog # CFB7G4

Galvanized Stamped Steel Floor Box, Recessed, 7-Gang CFB Series Box for Rectangular Cover, 4.08" Minumum Depth of Pour

Features

- Recessed 7-Gang Round Cover Floorbox
- For Use In Concrete Floors
- 4.08" Minimum Depth of Pour
- Box Includes Installation Cover
- Accepts industry Standard Size Wallplates

Application

- For Use in Concrete Floors

General

Application - For Use On	Concrete
Catalog Number	CFB7G4
Color	Metallic
Construction	Fabricated
EU RoHS Indicator	No
Knockouts	11) 1" - 1 1/2" , 1) 2"
Material	Pre Galvanized Steel
Mounting Method	Cast Into Concrete
Number of Gang(s)	7-Gang
Series	Recessed Rectangular - CFB Series
Size	7-Gang
Specifications	Min. Depth of Pour - 4.08" (103.5)
Type	7-Gang Recessed Floor Box
UPC	783585315881

Dimensions

Dimensions	10 in x 12.08 in x 4.08 in
Height	4.08 in
Length	10 in
Width	12.08 in

Conductor Related

Cable Entry	Through Cover

Certifications And Compliance

Industry Standard(s)	• UL/CSA • UL514

Logistics

Carton Quantity	1
Pallet Quantity	90

Product Assets

Brochures - Floorbox Selection Guide
Catalog Page - PREM T18 CatalogPage
Catalog Page - WDK O-37 Catalog Page
Catalogs - Premise Wiring Catalog
Catalogs - WDK Catalog Full 2024
Specifications - CFB7G4

©2024 Hubbell Incorporated. All rights reserved