

**IMPORTANT SAFETY INFORMATION. READ AND FOLLOW ALL SAFETY INSTRUCTIONS.** Follow label information and instructions concerning Wet or Damp Locations, installation near combustible materials, insulation, building materials, and proper lamping. Do not install in areas subject to combustible vapors or gases. Before wiring to power supply and during servicing or relamping, turn off power at fuse or circuit breaker. **All servicing or relamping must be performed by qualified service personnel. Product must be grounded to avoid potential electric shock or other potential hazard. Product must be mounted in locations and at heights and in a manner consistent with its intended use, and in compliance with the National Electrical Code and local codes.** The use of accessory equipment not recommended by the manufacturer or installed contrary to instructions may cause an unsafe condition. Do not block light emanating from product in whole or part, as this may cause an unsafe condition. Do not allow items such as drapes, curtains, screens or the like to come into contact with the product or to block light from the product, as this may cause an unsafe condition.

## INSTALLATION INSTRUCTIONS RMN4-120

\*\*\*\*\*  
**WARNING:** When using Special Control Devices with this Fixture, follow Instructions carefully to assure N.E.C. compliances. For more help, contact a Qualified Electrical Contractor.

**RISK OF FIRE:** Recessed portions of Recessed Housing, other than at points of support, shall be spaced at least 1/2 inch from combustible material. Thermal Insulation shall not be installed within (3) inches of Recessed Housing or Junction Box, and shall not be installed above the Fixture, as to entrap heat and prevent free circulation of air.

**CAUTION:** To complete the Installation, choose only a UL Listed Prescolite Trim from the Label inside the Housing. The use of any Trim Not Listed in this Fixture, is a Violation of N.E.C. Article 110-3 (B) and Voids All Warranties.

\*\*\*\*\*  
Follow this Instruction Sheet Carefully. Be sure Electricity is OFF before starting Installation.

1. Cut a 4 1/2 inch diameter Hole (1) in Ceiling and pull electrical Supply Cable (2) down through opening.

**CAUTION:** Be careful not to cut through Joists, Wiring or Piping when cutting opening in Ceiling.

2. Remove Cover Plate (3) from Junction Box (4). Select a UL listed Connector (5)(NOT FURNISHED) appropriate for the Electrical Supply Cable at installation. Remove desired Knockout (6) from Junction Box (4) and secure Cable (2) to Box with Connector (5).

3. Connect Fixture Wires (7) to Supply Wires (8) as shown in Wiring Diagram. Replace Cover Plate (3) onto Junction Box (4) securing in place with Cover Screw (9).

4. Slip Fixture Assembly up through Ceiling opening with flange (11) up against Ceiling. Make sure that Straps (13) are laying vertically against Housing (10) so that unit can pass through Ceiling opening. Loosen Wingnuts (12), rotate and slide Straps (13) down and secure against top of Ceiling surface. Tighten Wingnuts (12).

