

IMPORTANT SAFETY INFORMATION. READ AND FOLLOW ALL SAFETY INSTRUCTIONS. Follow label information and instructions concerning Wet or Damp Locations, installation near combustible materials, insulation, building materials, and proper lamping. Do not install in areas subject to combustible vapors or gases. Before wiring to power supply and during servicing or relamping, turn off power at fuse or circuit breaker. **All servicing or relamping must be performed by qualified service personnel. Product must be grounded to avoid potential electric shock or other potential hazard. Product must be mounted in locations and at heights and in a manner consistent with its intended use, and in compliance with the National Electrical Code and local codes.** The use of accessory equipment not recommended by the manufacturer or installed contrary to instructions may cause an unsafe condition. Do not block light emanating from product in whole or part, as this may cause an unsafe condition. Do not allow items such as drapes, curtains, screens or the like to come into contact with the product or to block light from the product, as this may cause an unsafe condition.

INSTALLATION INSTRUCTIONS ARCHITRAK® SYSTEM

INSTALLATION INSTRUCTIONS

FOR PRESCOLITE AKT TRACK FIXTURE ASSEMBLIES

FOR USE WITH PRESCOLITE AKT ONE/TWO CIRCUIT TRACK SYSTEM ONLY

READ INSTALLATION INSTRUCTIONS BEFORE INSTALLING THE TRACK SYSTEM

SAVE INSTRUCTIONS FOR REFERENCE WHEN MAKING ADDITIONS TO OR CHANGES IN THE TRACK SYSTEM

INSTALLATION

TRACK WIRED FOR SINGLE CIRCUIT OPERATION.

1. Refer to PRESCOLITE AKT series track for track installation instructions.
2. Pull plastic cover down on fixture contact head.
3. Insert contact head into PRESCOLITE AKT TRACK RAIL. Twist contact head 1/4 turn (90 degrees) until locking tab snaps up into place. To remove fixture from track, retract locking tab, turn 1/4 turn, (90 degrees) and remove.
4. If fixture assembly does not light, remove fixture, rotate 180 degrees, reinsert into track and turn 1/4 turn to engage single circuit.


TRACK WIRED FOR TWO CIRCUIT OPERATION.

1. All fixtures can be placed on circuit one or circuit two. To alternate circuits fixtures are placed on, rotate alternate fixture 180 degrees.
2. Refer to AKT TRACK RAIL INSTRUCTIONS for circuit identification groove.

NOTE: For lamp type and maximum lamp wattage, refer to relamp label located inside fixture assembly.

WARNING:

WHEN INSTALLING OR USING THIS TRACK SYSTEM, BASIC SAFETY PRECAUTIONS SHOULD ALWAYS BE FOLLOWED. READ ALL INSTRUCTIONS. DO NOT INSTALL THIS TRACK IN DAMP OR WET LOCATIONS. DO NOT INSTALL ANY PART OF TRACK SYSTEM LESS THAN 5 FEET ABOVE FLOOR. DO NOT INSTALL ANY FIXTURE ASSEMBLY CLOSER THAN 6 INCHES FROM ANY CURTAIN OR SIMILAR COMBUSTIBLE MATERIAL. DISCONNECT ELECTRICAL POWER BEFORE ADDING TO OR CHANGING THE CONFIGURATION OF THE TRACK. DO NOT ATTEMPT TO ENERGIZE ANYTHING OTHER THAN LIGHTING TRACK FIXTURES ON THE TRACK. TO REDUCE THE RISK FIRE AND ELECTRICAL SHOCK, DO NOT ATTEMPT TO CONNECT POWER TOOLS, EXTENSION CORDS, APPLIANCES, AND THE LIKE TO THE TRACK.



**FIXTURE ASSEMBLY
NOT SHOWN
SAVE THESE INSTRUCTIONS**