HUBBELL
Premise Wiring

Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 7′ Length, Pink

By Hubbell Premise Wiring
Catalog # HC5EPK07

Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 7′ Length, Pink

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

Application

Category 5e

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC5EPK07
Color	Pink
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620235653

Dimensions

Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Product Assets

Literature - SPEEDGAIN Category 5e Enhanced Performance System
Sales Drawings - HC5EP - PDF
Specifications - HC5EPK07

©2024 Hubbell Incorporated. All rights reserved