HUBBELL
Premise Wiring

Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 100′ Length, Gray

By Hubbell Premise Wiring
Catalog # HC6AGY100

Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 100′ Length, Gray

Features

- Ascent
- Cat6A
- Slim
- 100′ Length
- Gray

Application

Category 6A

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6AGY100
Color	Gray
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620230092

Dimensions

Outside Diameter	0.218

Electrical Ratings

Voltage Rating	600V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Product Assets

Sales Drawings - HPW_HC6AGY_DRAWING_PDF
Specifications - HC6AGY100

©2024 Hubbell Incorporated. All rights reserved