HUBBELL
Premise Wiring

Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 75′ Length, Red

By Hubbell Premise Wiring
Catalog # HC6AR75

Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 75′ Length, Red

Features

- Ascent
- Cat6A
- Slim
- 75′ Length
- Red

Application

Category 6A

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6AR75
Color	Red
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620230962

Dimensions

Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Product Assets

Literature - NEXTSPEED® Category 6 OSP Cable
Sales Drawings - HC6AR - PDF
Specifications - HC6AR75

©2024 Hubbell Incorporated. All rights reserved