INSTALLATION INSTRUCTIONS	FIXTURE TYPE	WALLSLOT 6000 SYSTEM CONNECTORS	
Р/С <b>510593-0000</b>		STRAIGHT EXTENSION [SE]	
WHICH IS CONTRARY TO IF YOU HAVE ANY QUES	ER THIS PRODUCT IN ANY WAY, OR THE INSTRUCTIONS CONTAINED HE TIONS REGARDING THIS PRODUCT O ROL ENGINEERING AT 781-294-010	REIN. R THE INSTALLATION OF IT,	
NOTES: STRAIGHT EXTENSI	CONS (SE) ARE INSTALLED AT ENDS (	OF ROW TO CLOSE OFF CEILING OPENING.	
B. STRAIGHT EXTENSIONS C. REFER TO PAGES 3 FOR	STALLED PRIOR TO ATTACHING STRAIG ARE SHIPPED SEPARATELY AND BULK R INSTALLING 90 AND 135 DEGREE CO INSTALLING PLENUM END CAPS.	PACKAGED.	~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~
ADJACENT WALL SURFAC SAWCUT ENDS OF TRIM	ALLY POSITIONED IN ROW, MEASURE T CE SHOWN IN PLAN VIEW AS DIM "X". AS SHOWN TO DIM "X" (VIEW A). 2' (ONLY), TRIM PLENUM COVER TO A		SE HALF HOUSING
TIGHTEN SPLINE BY IN	SERTING MACHINE SCREW INTO PEM N	PLINES INTO GROOVE IN TRIM (VIEW B). UTS INCLUDED IN SPLINE (VIEW C). UNTING SCREWS (BY OTHERS) AS SEEN IN VIEW C.	
MACHINE SCREWS. BEND OPPOSITE TAB UP	D LAST FIXTURE AND CUT TRIM. SCREP TO AVOID INTERFERENCE WITH FIXT TAP TO TOP TAB OF SE HOUSING.	W DOWN SE HOUSING TO TRIM USING PROVIDED URE (VIEW B).	TRIM
PLACE PLENUM COVER O	COVER 90 DEGREES FOR MOUNTING. ONTO DOUBLE SIDED TAPE ONTO SE HO G MOUNTING SCREWS (PROVIDED BY OT		
	TRIM OFF		ITEMS SUPPLIED
		DIM "X"	
			DIM. X 2" MIN - 12" MAX.
	VIE	<u>EW A</u>	<u>PLAN VI</u>
LITECONTROL 11	tecontrol.com		









