



J-27N

Surface Mount J-27N Installation Instructions

⚠ WARNING: Fixtures must be grounded in accordance with local codes or the National Electrical Code. If Surface Mount is connected to a cord and plug, it must be plugged into a receptacle protected by a Ground Fault Circuit Interrupter (GFCI) in accordance with the National Electrical Code. Failure to take these steps may result in serious personal injury.



KEEP THIS SHEET FOR FUTURE REFERENCE.

Tools Required: Flat Blade Screwdriver RTV Sealant 3/32" Allen Wrench


Kim Surface Mount is supplied with (2) 1/2" N.P.S.M. female threads.

⚠ Make certain electrical supply is OFF before installing equipment.


1. Attach Surface Mount to wood structure or tree using wood screws of sufficient size for fixture weight and installation integrity. If mounting to a tree, space Surface Mount and conduit or cord 1" away from tree to allow for growth. Establish a regular maintenance schedule to insure tree growth does not damage or engulf electrical equipment.




2. Remove splice compartment cover and gasket.




3. Attach conduit or outdoor cord with weatherproof cord seal (by others). Seal threads.




4. Attach fixture. Seal threads.



5. Make wire connections observing polarity, i.e., green-to-ground, white-to-common and black-to-voltage.



6. Adjust fixture and secure with set screw.



7. Replace splice compartment cover and gasket.

Surface Mount J-27N Installation Instructions

KIM LIGHTING LIMITED WARRANTY

When installed in accordance with Kim Installation Instructions and accepted trade practices, the following shall apply:

General Product Limited Warranty Coverage

All material and component parts used in the manufacture of Kim Products, are warranted to be free from defects of material and/or workmanship for a period of 1 year from date of sale, with the following exceptions:

Auxiliary Equipment

All auxiliary equipment (such as lamps, ballasts, and transformers) provided by and/or included in Kim Products shall carry the component manufacturer's warranty.

Copper and Bronze Landscape Components

Copper and Bronze Landscape fixture components shall be warranted against defects of material and/or workmanship, and failure due to corrosion, for a period of 25 years from date of sale.

Composite In-Grade Components

Composite In-Grade fixture components installed below grade, shall be warranted against defects of material and/or workmanship, and failure due to corrosion, for a period of 7 years from date of sale.

Aluminum Landscape Components

Aluminum Landscape fixture components not in direct contact with soil, shall be warranted against defects of material and/or workmanship for a period of 3 years from date of sale. Aluminum fixture components in direct contact with soil shall be warranted from defects of material and failure from corrosion for a period of 1 year from date of sale.

Limit of Liability and General Conditions

Only products which are installed, used and maintained in accordance with applicable Kim instructions, specifications and accepted trade practices, are covered by the Kim Warranty. During the warranty period, with proof of purchase, Kim will repair or replace with the same or similar product, at Kim's option, without charge. Labor costs are the owner's responsibility and are excluded from this warranty. This warranty is void if the product is modified, tampered with, misapplied, poorly installed, improperly maintained, or subjected to abnormal conditions.

Repair or replacement as provided under this warranty is the exclusive remedy of the purchaser. This warranty is in lieu of all other warranties, expressed or implied, including any implied warranty of fitness for a particular application. Kim Lighting shall not be liable to the purchaser for indirect or consequential damages.



How may we serve you better?
Please let us know. Visit our website at:
www.kimlighting.com
Your concerns are important to us.