Mounted Zone Cabling Enclosures and Brackets

Industrial ReBox Enclosure with Equipment Mounting Brackets

NEMA 4/12 ReBox Enclosure

Features

- Continuous plasma-welded seams prodvide a seal to protect equipment from water intrusion
- Three-Point locked twist handle secures and applies pressure on door gasket for a water-tight seal
- Plywood back panel allows for fleixble mounting of equipment and cable management



Ordering Information

NEMA Rating	Finish	Catalog Number	UPC Number
4 / 12	Gray powder coated	**IR422PG**	662620656373

Listings

NEMA Rated 4 / 12
EIA/ECA-310-E Universal Mounting Pattern
UL Listed

Specifications

Material	Carbon Steel
Gauge	14
Finish	Light Gray
NEMA Rating	4 / 12
Rail Type	#12-24 Threaded
Rack Units	26

Dimensions- inches (mm)

A	48" (1219)
B	24" (610)
C	24" (610)

Accessories

12" foot Kit	**IRF1224**
5U Bracket	**REKZ**
Heater Thermostat	**CTKH**
250W Heater	**IRH250**
#12-24 Screws	**1224RRSCRW20**

Online Resources

Customer Use Drawing
eCatalog
Product Guide