HUBBELL
Premise Wiring

Copper Solutions, Cable, NEXTSPEED, 10GBE, Riser Rated, Spool, Gray

By Hubbell Premise Wiring
Catalog # C6ASRGY

Copper Solutions, Cable, NEXTSPEED, 10GBE, Riser Rated, Spool, Gray.

Features

- NEXTSPEED
- 10GBE
- Riser Rated
- Spool
- Gray

Application

Riser

General

Cable Rating	Riser
Catalog Number	C6ASRGY
Construction	Copper/Insulation Eccentricity Shall Be 90% Minimum
Data Transfer Rate	10GbE
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6A UTP Cable
Material - Jacket	PVC
Temperature Rating	-20oC to +50oC (-4oF to +122oF)
Type	UTP
UPC	662620202006

Electrical Ratings

Capacitance	5.6 nF/100 Meters @ 1 kHz
Impedance	100

Conductor Related

Conductor Size	#23 AWG
Conductor Type	Solid Bare Copper
Nema Color	Gray
Pairs Or Conductor	4-Pair

Logistics

Carton Quantity	1000

Product Assets

Catalog Page - PREM E4 CatalogPage
Catalogs - Premise Wiring Catalog
Specifications - C6ASRGY Specification Sheet French

©2024 Hubbell Incorporated. All rights reserved