



KIM LIGHTING

16555 East Gale Avenue
City of Industry, CA 91745-1788
626/968-5666 • FAX 626/968-5716



C24



HUBBELL
Lighting

C24 LED Accent Light Installation Instructions

INSTRUCTIONS PERTAINING TO A RISK OF FIRE, OR INJURY TO PERSONS IMPORTANT SAFETY INSTRUCTIONS!

⚠ WARNING: Fixtures must be grounded in accordance with local codes or the National Electrical Code. Portable spear or tree mounts using a cord and plug must be plugged into a receptacle protected by a Ground Fault Circuit Interrupter (GFCI) in accordance with the National Electrical Code. Failure to take these steps may result in serious personal injury. Lighted lamp is HOT!

⚠ AVERTISSEMENT: Les luminaires doivent être mis à la terre conformément aux codes locaux ou au National Electrical Code. Lance ou arbres supports portables utilisant un cordon et la prise doivent être branchés dans une prise protégée par un disjoncteur différentiel (GFCI) conformément au Code national de l'électricité. Le défaut de prendre ces mesures peut entraîner des blessures graves. La lampe allumée est CHAUD!

⚠ NOTE: All wiring must be done by a qualified electrician.

⚠ REMARQUE: Tout le câblage doit être fait par un électricien certifié.

See additional warnings and cautions on p. 3.


KEEP THIS SHEET FOR FUTURE REFERENCE.

Your KIM fixture is supplied with 1/2" NPSM male mounting threads and locknut.*

Tools Required: Flat Blade Screwdriver Thread Sealant 3/32" Allen Wrench

⚠ Make certain the electrical supply is **OFF** before starting fixture installation.

⚠ Assurez-vous que l'alimentation électrique est coupée avant l'installation du luminaire.



1. Apply thread sealant onto exposed fixture threads to keep moisture from entering junction box. Thread fixture onto junction box cover or mounting device.




2. Attach fixture leads to circuit leads observing polarity, i.e.; green-to-ground, white-to-common and black-to-voltage with wire connectors by others.




3. Tighten locknut to ensure selected orientation. Tighten screw under J-Box cover, (if supplied), to secure fixture. Attach cover.

*Consult Kim Landscape Lighting Collection Catalog for mounting device options.

C24 LED Accent Light Installation Instructions




4. Loosen set screw and swivel screw, but do not disengage. Hold fixture at desired angle and tighten





swivel screw firmly. Tighten set screw firmly to lock angle adjustment of fixture.


C24 LED Accent Light Installation Instructions


Installation warnings and cautions for standard product Avertissements d'installation et mises en garde


 **WARNING:** Make certain all electrical supply is OFF before starting installation or beginning maintenance procedures.


 **AVERTISSEMENT:** S'assurer que toute alimentation possible est COUPÉE avant de commencer l'installation ou l'entretien.


 **WARNING:** Fixtures must be grounded in accordance with local codes or the National Electrical Code. Failure to do so may result in serious personal injury.


 **AVERTISSEMENT:** Les appareils doivent être mis à la terre en conformité avec le Code canadien de l'électricité et les codes locaux. Une non-conformité pourrait conduire à des blessures graves.


 **WARNING:** To prevent wiring damage or abrasion, do not expose wiring to edges of sheet metal or other sharp objects.


 **AVERTISSEMENT:** Pour empêcher l'endommagement ou l'éraflure des fils, empêchez tout contact avec les rebords des parties métalliques.


 **MAINTENANCE:** A regularly scheduled maintenance program should be established to retain optimum light output and reduce heat retention. Dusting with a soft, clean, dry cloth is normally sufficient for the reflector.


 **ENTRETIEN:** Un programme d'entretien régulier devrait être établi pour conserver la luminosité optimale et réduire l'accumulation de chaleur. Un chiffon doux et propre est normalement suffisant pour dépoussiérer le réflecteur optique. Ne pas utiliser de produit nettoyant alcalin ou acide sur les surfaces du réflecteur.


 **NOTE:** All wiring must be done by a qualified electrician.

 **REMARQUE:** Tout le câblage doit être fait par un électricien certifié.


 **CAUTION:** LED fixtures are available in 120 volt input or 277volt input. Please verify before wiring fixture to field wires. (see lamp label to verify).


 **MISE EN GARDE:** Les appareils d'éclairage à DEL sont offerts pour alimentation à 120 V ou 277 V. Veuillez vérifier avant de raccorder (voir l'étiquette de l'appareil pour confirmer).

 **CAUTION:** Do not alter, relocate, or remove wiring, lampholders, ballasts, or any other electrical components.


 **ATTENTION:** Ne pas modifier, déplacer ni enlever de câble, de douille de lampe, de ballast ou autre composant électrique.

 **Additional Warnings**
Avvertissements supplémentaires


 **CAUTION:** To help maintain a clean, dry splice compartment, seal the conduit entries with RTV.


 **MISE EN GARDE:** Pour garder le compartiment de jonction des fils propre et sec, scellez les entrées de conduits avec du composé RTV.


For Landscape fixtures

 **WARNING:** Portable spear or tree mounts using a cord and plug must be plugged into a receptacle protected by a Ground Fault Circuit Interrupter (GFCI) in accordance with the National Electrical Code. Failure to do so may result in serious personal injury.

Pour appareils d'aménagement paysager

 **AVERTISSEMENT:** Selon le Code national de l'électricité, les appareils portatifs de type lance ou pour montage dans les arbres qui sont munis de cordon et fiche, doivent être branchés dans une prise à protection par disjoncteur de mise à la terre. Une non-conformité pourrait conduire à des blessures graves.

 **CAUTION:** Particular care should be taken not to locate fixtures where small children can reach them if higher wattages are used.

 **MISE EN GARDE:** Une attention particulière devrait être portée pour ne pas installer les appareils d'éclairage dans les endroits accessibles par les jeunes enfants, spécialement si la puissance de l'ampoule est élevée.

KEEP THIS SHEET FOR FUTURE REFERENCE.

CONSERVER LA PRÉSENTE FEUILLE POUR RÉFÉRENCE ULTÉRIEURE.

C24 LED Accent Light Installation Instructions

KIM LIGHTING LIMITED WARRANTY

When installed in accordance with Kim Installation Instructions and accepted trade practices, the following shall apply:

General Product Limited Warranty Coverage

All material and component parts used in the manufacture of Kim Products, are warranted to be free from defects of material and/or workmanship for a period of 1 year from date of sale, with the following exceptions:

Auxiliary Equipment

All auxiliary equipment (such as lamps, ballasts, and transformers) provided by and/or included in Kim Products shall carry the component manufacturer's warranty.

Copper, Bronze and Brass Landscape Components

Copper and Bronze Landscape fixture components shall be warranted against defects of material and/or workmanship, and failure due to corrosion, for a period of 25 years from date of sale.

Kim Lighting's Brass components are constructed from several brass parts that are manufactured by various methods at various times. Since brass naturally deepens in color as it ages through the normal oxidation process, these parts may exhibit subtle differences in coloration when the product is new. This is normal and expected. These color differences will be eliminated shortly after installation through the normal brass oxidation process.

Composite In-Grade Components

Composite In-Grade fixture components installed below grade, shall be warranted against defects of material and/or workmanship, and failure due to corrosion, for a period of 7 years from date of sale.

Aluminum Landscape Components

Aluminum Landscape fixture components not in direct contact with soil, shall be warranted against defects of material and/or workmanship for a period of 3 years from date of sale. Aluminum fixture components in direct contact with soil shall be warranted from defects of material and failure from corrosion for a period of 1 year from date of sale.

Limit of Liability and General Conditions

Only products which are installed, used and maintained in accordance with applicable Kim instructions, specifications and accepted trade practices, are covered by the Kim Warranty. During the warranty period, with proof of purchase, Kim will repair or replace with the same or similar product, at Kim's option, without charge. Labor costs are the owner's responsibility and are excluded from this warranty. This warranty is void if the product is modified, tampered with, misapplied, poorly installed, improperly maintained, or subjected to abnormal conditions.

Repair or replacement as provided under this warranty is the exclusive remedy of the purchaser. This warranty is in lieu of all other warranties, expressed or implied, including any implied warranty of fitness for a particular application. Kim Lighting shall not be liable to the purchaser for indirect or consequential damages.

How may we serve you better? Please let us know.
Visit our website at: www.kimlighting.com
Your concerns are important to us

