



KIM LIGHTING

16555 East Gale Avenue
City of Industry, CA 91745-1788
626/968-5666 • FAX 626/968-5716



HUBBELL
Lighting

Ravenna LED 12V Installation Instructions

INSTRUCTIONS PERTAINING TO A RISK OF FIRE OR INJURY TO PERSONS IMPORTANT SAFETY INSTRUCTIONS!

WARNING: To reduce the risk of FIRE OR INJURY TO PERSONS: Do not overdrive fixtures with greater than 12 volts or fixture over-heating and short lamp life will occur. Do not overload the transformer by installing (or relamping) higher wattage lamps than planned. Note: Total wattage of all lamps connected to one transformer must not exceed the capacity of that transformer. Do not install luminaire within 10 feet (3.04m) of a pool, spa or fountain.

SAFETY WARNING: When relamping, be sure electrical supply is OFF. Use discretion when touching fixture and be sure to allow fixture to cool before relamping. When relamping fixture avoid touching the lamp envelope with bare hands.

MAINTENANCE: To maintain light efficiency and prevent fixture-overheating, glass lenses and enclosure must be kept clean and free of dirt, dust, leaves, trash (combustible materials) and mineral deposits from water. Particular care should be taken not to locate fixtures where small children can reach them if higher wattages are used.

KEEP THIS SHEET FOR FUTURE REFERENCE.



KLVL276
KLVL271


KLVL176
KLVL171

- Tools Required:**
- 1/8" Hex Wrench
 - 5/64" Hex Wrench
 - Your KIM fixture is supplied with 1/2" NPSM male mounting threads.
 - Silicone Grease
 - 3/16" Hex Wrench
 - Adjustable Wrench

! Make certain the electrical supply is **OFF** before starting fixture installation.



1. Tighten coupling onto mounting device*.



2. Install fixture onto coupling. Attach fixture cable to main system cable with a KLV410 connector.



3. Loosen setscrew, adjust fixture rotation, and tighten setscrew.

IMPORTANT: Do not overload the transformer by installing higher wattage lamps than planned. Remember, the total wattage of all lamps connected to one transformer must not exceed the capacity of that transformer.

IMPORTANT: When fixtures are aimed up, particular care should be taken to keep lens free of debris and mineral deposits. When fixtures are in an area where debris or mineral deposits are likely to be a problem, lower wattage lamps should be used, and lenses should be cleaned on a regular maintenance schedule.

*Consult Kim Landscape Lighting Collection Catalog for mounting device options.

Ravenna LED 12V Installation Instructions

Additional wire and connectors may be purchased from Kim Lighting:

KLV427 #12-2 Cable KLV410 Connector
KLV432 #8-2 Cable KLV411 Connector

KIM LIGHTING LIMITED WARRANTY

When installed in accordance with Kim Installation Instructions and accepted trade practices, the following shall apply:

General Product Limited Warranty Coverage

All material and component parts used in the manufacture of Kim Products, are warranted to be free from defects of material and/or workmanship for a period of 1 year from date of sale, with the following exceptions:

Auxiliary Equipment

All auxiliary equipment (such as lamps, ballasts, and transformers) provided by and/or included in Kim Products shall carry the component manufacturer's warranty.

Copper and Bronze Landscape Components

Copper and Bronze Landscape fixture components shall be warranted against defects of material and/or workmanship, and failure due to corrosion, for a period of 25 years from date of sale.

Composite In-Grade Components

Composite In-Grade fixture components installed below grade, shall be warranted against defects of material and/or workmanship, and failure due to corrosion, for a period of 7 years from date of sale.

Aluminum Landscape Components

Aluminum Landscape fixture components not in direct contact with soil, shall be warranted against defects of material and/or workmanship for a period of 3 years from date of sale. Aluminum fixture components in direct contact with soil shall be warranted from defects of material and failure from corrosion for a period of 1 year from date of sale.

Limit of Liability and General Conditions

Only products which are installed, used and maintained in accordance with applicable Kim instructions, specifications and accepted trade practices, are covered by the Kim Warranty. During the warranty period, with proof of purchase, Kim will repair or replace with the same or similar product, at Kim's option, without charge. Labor costs are the owner's responsibility and are excluded from this warranty. This warranty is void if the product is modified, tampered with, misapplied, poorly installed, improperly maintained, or subjected to abnormal conditions.

Repair or replacement as provided under this warranty is the exclusive remedy of the purchaser. This warranty is in lieu of all other warranties, expressed or implied, including any implied warranty of fitness for a particular application. Kim Lighting shall not be liable to the purchaser for indirect or consequential damages.

How may we serve you better? Please let us know.
Visit our website at: www.kimlighting.com
Your concerns are important to us

