HUBBELL
Premise Wiring

Fiber Optic Panel Adapter, 24-Fiber, 6 LC Quad, Phosphor Zircon Sleeves, Beige

By Hubbell Premise Wiring
Catalog # FSPNLCQS6BE

Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Beige

Features

- Premium Quality and High Performance Design

Application

Interconnect

Specifications

Industry Standard(s)	• TIA-568-C.3 • TIA-604-FOCIS

Conductor

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Configuration

Number Of Ports	24

Current

Insertion Loss	0.30 dB
Return Loss	55

General

Color	Beige
UPC	662620340074
Material - Mounting Hardware	Snap-In
Sub Brand	OptiChannel
Material	Ceramic Zirconium

Logistics

Carton Quantity	4

Operational

Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	SM/MM
Adapter Type	LC Quad
Temperature Rating	-40C to +85C

Product Assets

Catalog [English]
Catalog Page [English]
Catalog Page [English]

© 2026 Hubbell Incorporated. All rights reserved