HUBBELL
Premise Wiring

FSP Adapter Panel, SC Duplex/ST-Style, 12-Port, Loaded with 6 Adapters, Phosphor Bronze

By Hubbell Premise Wiring
Catalog # FSPSCST6

FSP Adapter Panel, SC Duplex/ST-Style, 12-Port, Loaded with 6 Adapters, Phosphor Bronze.

Features

Premium Quality and High Performance Design

Application

Interconnect

Performance

- Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 ºC to +75 ºC

General

Adapter Type	SC to ST Duplex
Catalog Number	FSPSCST6
Color	Blue
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	SC to ST Duplex
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Specifications	• Dimensions - 1.1” W X 5.1” H • Finish - Durable black powder coat • Material - 16ga cold rolled steel • Sleeve Material - Phosphor Bronze
Temperature Rating	-40C to +85C
UPC	662620816913

Dimensions

Display Size	5.1″ X 1.1″

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	26

Conductor Related

Fiber Size	125 Micron
Fiber Type	Multimode

Certifications And Compliance

Industry Standard(s)	• TIA-568-C.3 • TIA-604-FOCIS

Logistics

Carton Quantity	4

Product Assets

Specifications - FSPSCST6 Specification Sheet French

©2024 Hubbell Incorporated. All rights reserved