CHANCE Anchor Installation Tools

Product Feature & Selection Guide







www.HPSdelivers.com/Anchors



CHANCE[®] **Anchors** were the first to be used in the utility industry and today are an international leader in earth anchoring, guying utility and communication poles and providing foundations for towers and heavy equipment.

Engineered for dependability and long-term stability, Hubbell manufactures these products featuring exclusive anchoring techniques, tools, designs and sizes which improve the efficiency and durability of electrical and communication structures.

As digger derrick trucks continue to get bigger with larger more powerful digger motors, CHANCE anchor tools are the only tools available that can safely install anchors rated at up to 15,000 ft-lbs of torque.

Ensure your crews are ready to properly and safely install anchors by selecting CHANCE anchors and installation tooling.

Trust the tools from the company who gives you:

- Free access to HeliCAP[®] design software for engineering anchors and foundations with predictable capacity
- Engineering support for product training
- Field installation advice
- Anchoring seminars with classroom, test lab and field installation and testing.
- Free application-specific product recommendations
- A broad library of anchoring resources, both online and in print, including The Encyclopedia of Anchoring.
- The CHANCE Digital Torque Indicator, which lets you install screw anchors to a pre-determined torque value, giving a positive indication of anchor holding capacity in any soil type.



3

Anchor Installation Tools

CHANCE anchor tooling comes in two sizes to allow you to right-size installation tools for your truck and application. Standard Tooling has a installation torque rating of 10,000 ft-lb. of torque. CHANCE Tough One® tooling has an installation torque rating of 15,000 ft. lb.

Truck digger motor and Kelly bar

KELLY BAR ADAPTER

Torque Rating	Kelly Bar Shape	Kelly Bar Size	Bolt Circle Diameter
10,000 10,000 10,000	Hex Hex Hex	2" 2½" 25⁄8"	5 1/4" 5 1/4" 5 1/4"
15,000 15,000 15,000 15,000 15,000 15,000	Hex Hex Hex Square Square Square	2½" 25%" 3" 2½" 3" 3½"	7 5/8" 7 5/8" 7 5/8" 7 5/8" 7 5/8" 7 5/8" 7 5/8"
	Rating 10,000 10,000 10,000 15,000 15,000 15,000 15,000	Rating Shape 10,000 Hex 10,000 Hex 10,000 Hex 10,000 Hex 15,000 Hex 15,000 Hex 15,000 Hex 15,000 Square 15,000 Square	RatingShapeSize10,000Hex2"10,000Hex2½"10,000Hex2½"10,000Hex2½"15,000Hex2½"15,000Hex3"15,000Square2½"15,000Square3"

LOCKING	DOG		
Part No.	Torque Rating	Description	Bolt Circle Diameter
C3030069HD	10,000	Complete Assembly	5 1/4"
C3030070	10,000	Replacement Kit	5 1/4"
P1300007P	10,000	Replacement Ring	5 1/4"
C3030981	15,000	Complete Assembly	7 5/8"
C3031026	15,000	Replacement Kit	7 5/8"

DRIVE W	RENCH			
Part No.	Torque Rating	Length (ft)	Color Code	Locking Dog
C1021583	10,000	7	Orange	C3030069HD
C1021595	10,000	3 1/2	Orange	C3030069HD
C3031064	10,000	7	Yellow	C3030069HD
C3031063	10,000	3 1/2	Yellow	C3030069HD
C3030983	15,000	7	Red	C3030981
C3030982	15,000	3 1/2	Red	C3030981

Search any catalog number or product name on www.hubbellpowersystems.com for complete details, instructions, and ordering information.

TORQUE INDICATOR

Optional but recommended **Part No.** C3031836


ANCHOR-

4

PISA® ROD


How to Match Anchors and Installing Wrenches

p15h c Anchor	stall pisk T Anchor	Mia	C102-52 Anchor Shine One Anchor Shine One Anchor Anchor	C102-54, chor 5. One Anchor Tough	C102-50, Anchor Lough One® Anchor Lough	C102-50/ Lord One Anchor Lord One Anchor Lord Tough	XX Series Tough					ſ		Ð.	
ł	ł	ł	ł	P	Ţ	Ţ	P	Installing Wrench Catalog Number	Length (ft)	Maximum Installing Torque Rating (ft-lb)	g Outside		Inside Dimension (in)		Fits Locking Dog Assembly
								C1021583 7 10,C	10,000 2		2.16		16	C3030069HD	
								C1021595	31⁄2	10,000	2.16 1.4		16	C3030069HD	
								C3031064	7	10,000	<u>Top</u> 2.16	<u>Bot</u> 2.44	<u>Top</u> 1.46	<u>Bot</u> 1.54	C3030069HD
											Tau		-	Det	
								C3031063	31/2	10,000	<u>Top</u> 2.16	<u>Bot</u> 2.44	<u>Top</u> 1.46	<u>Bot</u> 1.54	C3030069HD
								 C3031063 C3030983	3½ 7	10,000 15,000	2.16	<u>Bot</u> 2.44 44	<u>10p</u> 1.46 1.5	1.54	C3030069HD C3030981
								 			2.16 2.	2.44	1.46	1.54 54	



Installing wrenches are color coded based on their dimensions and torque rating for easy identification in the field.

Inside and outside dimensions correspond to the color coded end of installing wrench.







HUBBELL / CHANCE CENTRALIA, MISSOURI USA 210 North Allen Street Centralia, MO 65240

©Copyright 2023 Hubbell Incorporated. Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.

Printed in the U.S.A. | BR_06_167_E