HUBBELL
Premise Wiring

USOC netSELECT™ Jack

By Hubbell Premise Wiring
Catalog # NSJUY

NetSELECT™ RJ25 USOC modular jacks support various telephony applications. The innovative angled QuickLace™ termination towers provide ample room for lacing, accelerating the termination.

Features

- Easy To Terminate Angled Wiring Towers
- RJ25 USOC Telephone Jack

Performance

USOC

General

Catalog Number	NSJUY
Construction Material - Main	Thermoplastic
Contact	IDC: Phosphor Bronze with 100 Micro-Inch Tin Over Plating
Contact Point Material	Beryllium Copper with Gold Over Plating
EU RoHS Indicator	Yes
Item Type	Modular Jack
Material - Housing	High-impact thermoplastic (UL 94V-0)
Material - Mounting Hardware	Screw Mounting
Operating Cycles	750+ Plug
Series	USOC
Size	0.86 (22) x 0.67 (17) x 1.29 (33)
Specifications	• Housing - High impact thermoplastic (UL 94 V-0) • IDC Contact - Phosphor bronze with 100 micro-inch tin over nickel under plating • Nose Contact - Beryllium copper with precious metal plating with nickel under-plating
Style	RJ-45 Jack
Temperature Rating	Max Continu- 75° C, Minimum- -40° C Sans impact
UPC	883778503108

Dimensions

Display Size	Standard Sized Product

Electrical Ratings

Connectivity	RJ45 Jack to IDC Punch Down
Contact Resistance	Per TIA
Insertion Loss	Per TIA
Withstand Voltage	1,000 Vac @ 60 Hz

Certifications And Compliance

Industry Standard(s)	• 6-Position USOC Compliant • CSA Certified • Mechanical TIA-568 • RoHS Compliant • UL Listed 1873
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
Number of Pieces in Package	1

Product Assets

Catalog Page - PREM V10 CatalogPage
Catalog Page - PREM S10 CatalogPage
Catalogs - Premise Wiring Catalog
Specifications - NSJUY Specification Sheet French

©2024 Hubbell Incorporated. All rights reserved