

Premium Conductive Suits & Accessories

Suits, gloves, bonding clamps, and boots for barehand live-line work

Features:

- Carraro Tecno's patented silver thread design offers superior conductivity
- Meet IEC 60895:2020 class 1 standards
- Arc flashing rating of 13 cal/cm²
- Maintains conductivity after laundering
- Carrying and storage case included
- Quick Draw Clamp for reliable engagement and disengagement
- Conductive gloves with exclusive grip patches for secure grip
- Top-quality Italian leather boots



Ordering Information

Size	Height (in/cm)	Chest (in/cm)	Waist (in/cm)	Catalog Number
S	64-67 (164-170)	33-36 (84-92)	30-33 (76-84)	PSCFA32S
M	67-69 (170-176)	36-39 (92-100)	33-36 (84-92)	PSCFA32M
L	69-72 (176-182)	39-42 (100-108)	36-39 (92-100)	PSCFA32L
XL	72-74 (182-188)	42-46 (108-116)	39-42 (100-108)	PSCFA32XL
XXL	72-75 (184-190)	46-49 (116-124)	42-46 (108-116)	PSCFA322XL
XXXL	75-78 (192-198)	49-52 (124-132)	46-49 (116-124)	PSCFA323XL


AVAILABLE ACCESSORIES



Conductive
Socks



Conductive Boots,
Half-Height w/
Braided Copper
Leads & Calf Straps



Quick Draw
Clamp w/
Copper Lead



Conductive
Gloves w/
Grip Patches



Quick Draw
Bonding Clamp
(strap not included)



Conductive
Bonding Straps
(Pair)



Conductive Socks, Pair

Size	Catalog Number
M	PSCFE47M
L	PSCFE47L
XL	PSCFE47XL




Quick Draw Bonding Clamp

PSCFL50BS



Conductive Gloves, Pair

Size	Catalog Number
L	PSCFE46L
XL	PSCFE46XL



Quick Draw Clamp w/ Copper Lead

PSCFL50CU



Conductive Boots

Size	Catalog Number
8	PSCFA628
8.5	PSCFA6285
9	PSCFA629
9.5	PSCFA6295
10	PSCFA6210
10.5	PSCFA62105
11	PSCFA6211
11.5	PSCFA62115
12	PSCFA6212
13	PSCFA6213



Conductive Bonding Straps, Pair

PSCFE99



A Hubbell brand

©2024 Hubbell Power Systems. All rights reserved.
Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell
Incorporated. All other trademarks are the property of their respective owners.
210 N. Allen Centralia, MO 65240
www.hubbellpowersystems.com | hpscs@hubbell.com | 573-682-5521

CENT-LTE-SF-EN-02410 | 07/2025