

## AV and Power Ceiling Boxes


The AV Ceiling Enclosure is designed to house active AV devices and integrate AV distribution, data connections and power in one location, providing a direct connection to a projector or a display device. The enclosure protects and conceals your equipment and connections for a clean installation while maintaining accessibility with the hinged access doors.

### FEATURES

- Neatly Manage A/V, power, and data requirements inside one enclosure
- Two Enclosures Sizes to Match your Required Application
- Flush mounted, white enclosure for consistent look when mounted in the ceiling
- Hinged access doors accepts field installed ceiling tiles
- Enclosures with 1-1/2" conduit hubs for projector mounting
- All steel rugged construction provides the ultimate strength for installation



HRCB12WHT



HRCB22PWHT



AVCE1H



## 1' X 2' PLENUM RATED CEILING BOXES

Description	Length	Width	Height	Color	Catalog Number
Recessed ceiling box	23.69" (601.7mm)	23.69" (601.7mm)	6.00" (152.4mm)	White	<b>HRCB12WHT</b>
Recessed ceiling box with 1-1/2" NPT projector pole adapter	23.69" (601.7mm)	23.69" (601.7mm)	6.00" (152.4mm)	White	<b>HRCB12PWHT</b>
HRCB12 Series Box hard ceiling frame kit	23.57" (598.7mm)	24.94" (633.5mm)	7.38" (187.4mm)	White Flange	<b>HRCB12HCFK</b>
HRCB12 series box cooling fan kit	9.54" (242.3mm)	1.89" (48.1mm)	4.89" (124.2mm)		<b>HRCB12FAN</b>

Note: 1' x 2' ceiling boxes includes; (1) external 15A, 125V single receptacle and internal (2) 15A, 125V leaded duplex receptacles.

## 2' X 2' PLENUM RATED CEILING BOXES

Description	Length	Width	Height	Color	Catalog Number
Recessed ceiling box	23.69" (601.7mm)	23.69" (601.7mm)	6.00" (152.4mm)	White	<b>HRCB22WHT</b>
Recessed ceiling box with 1-1/2" NPT projector pole adapter	23.69" (601.7mm)	23.69" (601.7mm)	6.00" (152.4mm)	White	<b>HRCB22PWHT</b>
HRCB22 Series Box hard ceiling frame kit	23.57" (598.7mm)	24.94" (633.5mm)	7.38" (187.4mm)	White Flange	<b>HRCB22HCFK</b>
HRCB22 series box cooling fan kit	9.54" (242.3mm)	1.89" (48.1mm)	4.89" (124.2mm)		<b>HRCB22FAN</b>

Note: 2' x 2' ceiling boxes includes; (1) external switched 15A, 125V single receptacle and internal (5) 15A, 125V leaded duplex receptacles.

## 1' X 2' & 2' X 2" CEILING BOX ACCESSORIES

Description	Length	Width	Height	Size	Catalog Number
Ceiling box cable support kit, 4 cables	95" (2413.0mm)			0.09" (2.4mm)	<b>HRCB22WHT</b>
Ceiling box threaded rod kit, 4 brackets	0.88" (22.2mm)	0.06" (1.6mm)	1.19" (30.2mm)	Dia Up to 3/8" Threaded Rod	<b>HRCB22PWHT</b>

## AV CEILING ENCLOSURE

- Manage multiple applications inside one enclosure
- Flush mounted, white enclosure for consistent look when mounted in the ceiling
- Loaded with two Hubbell 20A duplex receptacles and a 2-gang back box
- All steel rugged construction provides the ultimate strength for installation



Description	Length	Width	Height	Color	Catalog Number
AV ceiling enclosure.	12" (305mm)	24" (610mm)	8" (203mm)	White	<b>AVCE1H</b>

For additional options and technical information, please see our full line catalog.



A proud member of the Hubbell family.

©2023 Hubbell Incorporated. All rights reserved.

Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated.

All other trademarks are the property of their respective owners.

hubbell.com/wiringdevice-kellems | 40 Waterview Drive, Shelton, CT 06484 | 800-288-6000

EP-WDK-SF-EN-01085 6/23