

PowerGain™ High Amperage Connections

Designed to meet the AI power demands of next-gen data centers, PowerGain™ delivers the reliable, high-amperage connections required to stay running at peak performance, enhanced with key requirements for safety, scalability, and seamless integration.

Made with highly engineered, heat-resistant materials, these Canadian-certified products include latching to prevent disconnect, labelling for circuit identification, and a flat design for wire management in, above, and under the cabinet.

Multiconductor Features

- cUL certification for Canada
- Impact resistant and non-conductive PBT housing
- Highly conductive, solid one-piece contacts
- Sequential contact engagement – ground first to make last to break
- Multiple terminal screws per contact
- Plugs and connectors have circuit identification labels (A, B, & white/blank)

Multiconductor Plugs

- Accept individual conductors, simplifying large-gauge wire management in tight spaces
- Replaceable latching module
- Oversized keying ground that prevents mismatching of unlike voltages and amperages

Multiconductor Connectors

- Highly conductive, multi-contact spring
- Integral NPS threads for use with cord connectors or flexible conduit fitting
- Integral mounting holes to secure connection in place



**Flat Panel Mount
Receptacle**



Flat Plug



Flat Connector



CSA C22.2 No. 182.1
UL1682



Scan to learn more

Ordering Information

PowerGain™ Plug

SKU	Description
HBL4125P250	PLUG, 4 WIRE, 125A, 250VAC
HBL5125P480	PLUG, 5 WIRE, 125A, 480VAC
HBL5125P415	PLUG, 5 WIRE, 125A, 415VAC
HBL5175P480*	PLUG, 5 WIRE, 175A, 480VAC
HBL5175P415*	PLUG, 5 WIRE, 175A, 415VAC

* Available soon

PowerGain™ Connector 1-1/4" Conduit

SKU	Description
HBL4125C250T125	CONNECTOR, 4 WIRE, 3P, 125A, 250VAC, 1-1/4" THREAD
HBL5125C480T125	CONNECTOR, 5 WIRE, 125A, 480VAC, 1-1/4" THREAD
HBL5125C415T125	CONNECTOR, 5 WIRE, 125A, 415VAC, 1-1/4" THREAD

PowerGain™ Connector 1-1/2" Conduit

SKU	Description
HBL4125C250T15	CONNECTOR, 4 WIRE, 3P, 125A, 250VAC, 1-1/2" THREAD
HBL5125C480T15	CONNECTOR, 5 WIRE, 125A, 480VAC, 1-1/2" THREAD
HBL5125C415T15	CONNECTOR, 5 WIRE, 125A, 415VAC, 1-1/2" THREAD

PowerGain™ Connector 2" Conduit

SKU	Description
HBL4125C250T2	CONNECTOR, 4 WIRE, 3P, 125A, 250VAC, 2" THREAD
HBL5125C480T2	CONNECTOR, 5 WIRE, 125A, 480VAC, 2" THREAD
HBL5125C415T2	CONNECTOR, 5 WIRE, 125A, 415VAC, 2" THREAD
HBL5175C480T2*	CONNECTOR, 5 WIRE, 175A, 415VAC, 2" THREAD
HBL5175C415T2*	CONNECTOR, 5 WIRE, 175A, 415VAC, 2" THREAD

* Available soon

PowerGain™ Receptacle

SKU	Description
HBL4125R250	RECEPTACLE, 4 WIRE, 3P, 125A, 250VAC
HBL5125R480	RECEPTACLE, 5 WIRE, 125A, 480VAC
HBL5125R415	RECEPTACLE, 5 WIRE, 125A, 415VAC
HBL5175R480*	RECEPTACLE, 5 WIRE, 125A, 480VAC
HBL5175R415*	RECEPTACLE, 5 WIRE, 125A, 415VAC

* Available soon

