



KIM LIGHTING

16555 East Gale Avenue
City of Industry, CA 91745-1788
626/968-5666 • FAX 626/968-5716



KLVL206



HUBBELL
Lighting

Accent Light - KLVL206 Installation Instructions

INSTRUCTIONS PERTAINING TO A RISK OF FIRE OR INJURY TO PERSONS

IMPORTANT SAFETY INSTRUCTIONS!

⚠ WARNING: To reduce the risk of FIRE OR INJURY TO PERSONS: **Do not overdrive fixtures with greater than 12 volts or fixture over-heating and short lamp life will occur. Do not overload the transformer by installing (or relamping) higher wattage lamps than planned. Note: Total wattage of all lamps connected to one transformer must not exceed the capacity of that transformer. Do not install luminaire within 10 feet (3.04m) of a pool, spa or fountain. DO NOT operate luminaire with missing or damaged lens.**

⚠ SAFETY WARNING: When relamping, be sure electrical supply is OFF. Use discretion when touching fixture and be sure to allow fixture to cool before relamping.

MAINTENANCE: To maintain light efficiency and prevent fixture-overheating, glass lenses and enclosure must be kept clean and free of dirt, dust, leaves, trash (combustible materials) and mineral deposits from water. Particular care should be taken not to locate fixtures where small children can reach them if higher wattages are used.

KEEP THIS SHEET FOR FUTURE REFERENCE.

Tools Required: Philips Screwdriver Flat Blade Screwdriver Adjustable Wrench
 1/8" Allen Wrench 3/16" Allen Wrench

⚠ Make certain the electrical supply is **OFF** before starting fixture installation.



1. Remove coupling from fixture.



2. Tighten coupling onto mounting device.



3. Install fixture onto coupling. Attach fixture leads.
Note: KIM KLV Mounting Options can be installed before fixture is attached.



4. Loosen set screw, adjust fixture rotation, and tighten set screw.

IMPORTANT: Do not overload the transformer by installing higher wattage fixtures than planned. Remember, the total wattage of all fixtures connected to one transformer must not exceed the capacity of that transformer.

IMPORTANT: When fixtures are aimed up, particular care should be taken to keep lens free of debris and mineral deposits. When fixtures are in an area where debris or mineral deposits are likely to be a problem, lower wattage lamps should be used, and lenses should be cleaned on a regular maintenance schedule.


*Consult Kim Landscape Lighting Collection Catalog for mounting device options.

Accent Light - KLVL206 Installation Instructions

Fixture Orientation



***Note:** Swivel stem must be installed with the mounting threads facing down-to-horizontal. Fixtures may not be installed with mounting threads facing upward unless shielded from rain or sprinklers.



5. To adjust angle, loosen swivel screw, do not disengage. Hold fixture at desired angle and tighten swivel screw. Fixture may be aimed up or down.

6. Connect fixture cable to main system cable with a sealed connector.

Additional wire and connectors may be purchased from Kim Lighting:

KLV427 #12-2 Cable KLV410 Connector
KLV432 #8-2 Cable KLV411 Connector

Note: Low voltage cable is intended for shallow burial, maximum of 6" (152 mm).

KIM LIGHTING LIMITED WARRANTY

When installed in accordance with Kim Installation Instructions and accepted trade practices, the following shall apply:

General Product Limited Warranty Coverage

All material and component parts used in the manufacture of Kim Products, are warranted to be free from defects of material and/or workmanship for a period of 1 year from date of sale, with the following exceptions:

Auxiliary Equipment

All auxiliary equipment (such as lamps, ballasts, and transformers) provided by and/or included in Kim Products shall carry the component manufacturer's warranty.

Copper and Bronze Landscape Components

Copper and Bronze Landscape fixture components shall be warranted against defects of material and/or workmanship, and failure due to corrosion, for a period of 25 years from date of sale.

Composite In-Grade Components

Composite In-Grade fixture components installed below grade, shall be warranted against defects of material and/or workmanship, and failure due to corrosion, for a period of 7 years from date of sale.

Aluminum Landscape Components

Aluminum Landscape fixture components not in direct contact with soil, shall be warranted against defects of material and/or workmanship for a period of 3 years from date of sale. Aluminum fixture components in direct contact with soil shall be warranted from defects of material and failure from corrosion for a period of 1 year from date of sale.

Limit of Liability and General Conditions

Only products which are installed, used and maintained in accordance with applicable Kim instructions, specifications and accepted trade practices, are covered by the Kim Warranty. During the warranty period, with proof of purchase, Kim will repair or replace with the same or similar product, at Kim's option, without charge. Labor costs are the owner's responsibility and are excluded from this warranty. This warranty is void if the product is modified, tampered with, misapplied, poorly installed, improperly maintained, or subjected to abnormal conditions.

Repair or replacement as provided under this warranty is the exclusive remedy of the purchaser. This warranty is in lieu of all other warranties, expressed or implied, including any implied warranty of fitness for a particular application. Kim Lighting shall not be liable to the purchaser for indirect or consequential damages.

How may we serve you better? Please let us know. Visit our website at: www.kimlighting.com. Your concerns are important to us

