1-Gang Weatherproof In-Use Cover, Expandable, Gray

By TayMac
Catalog # ML450G

1-Gang Weatherproof In-Use Cover, Expandable, Gray

Features

- Design expands from 1 in. to 3 in. for in-use needs
- Ultra rugged polycarbonate & synthetic neoprene rubber that will not dry rot, crack or deteriorate in sunlight
- Quick-Fit keyhole mounting system allows installation in under a minute
- Universal Fit Adapter System Technology (U-Fast) for 16-in-1 custom device configurations, comes pre-configured for GFCI
- Includes attached gasket and mounting hardware
- 100% paintable surface
- Clear window allows for quick/easy visual inspection
- Vertical or horizontal device mount

Application

In Use

General

Catalog Number	ML450G
Color	Gray
Construction	Nonmetallic
Cover Type	Expandable;In-Use
EU RoHS Indicator	Yes
Material	Polycarbonate
Mounting Method	Multi-directional
Number of Gang(s)	1-Gang
Type	Cover
UPC	092326111867
Weather Resistant	Yes

Dimensions

Cubic Capacity	73.6866 cu.in
Depth	3 in
Height	6.11 in
Weight	0.41 lb
Width	4.02 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	10
Packaging Type	Shrink
Pallet Quantity	1890
Standard Package	10

Product Assets

Brochures - HCC Products for Solar
Catalogs - RACO / TayMac / Bell Full Catalog
Catalogs - In-Use Covers and Conduit Bodies C1-C40_1
Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50
Certifications - UL COC-E116141-3
Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice
Sales Drawings - ML450
SDS - HCC SDS
Specifications - ML450G
Terms and Conditions - HCC Terms & Conditions
Video - TAYMAC: ML Series Expandable In-Use Covers

©2024 Hubbell Incorporated. All rights reserved