

HUBBELL iSTATION F-Connector Gold 3GHz



- Hubbell iSTATION System Integration
- Standard Hubbell Keystone Opening
- 3GHz Bandwidth Capacity
- RoHS Compliant



FEATURES

- High performance, gold plated F-connector
- 3 GHz bandwidth performance

SPECIFICATIONS

- Connector:
 - Connector body: brass
 - Gold plated: 2μ"
 - Type: female to female
- Material:
 - Snap Fit connector body: flame retardant high impact thermoplastic
 - Rated UL 94 V-0
- Cable type:
 - RG6
 - RG59

PERFORMANCE

- Electrical:
 - Range: 3GHz
 - Impedance: 75 Ohms
- Mechanical:
 - Mating Cycles: 500+

STANDARDS

- UL Listed 1863
- RoHS Compliant

Hubbell's AV Gold 3GHz F-Connectors provide a perfect solution for distributing coaxial (RG-6 and RG-59) video signals to flat panel TVs, monitors, projectors and smart-boards. Requiring no soldering, these F-connectors install with a snap and provide a quick easy "screw-on" or "push-on" termination.

These F-Connectors are available in five standard colors and mount into all Hubbell iSTATION face plates, modules, frames, surface housings, Hubbell Delivery System products, including poke-throughs, surface raceway and Hubbell iSTATION UDX multimedia panels.

Create a customized multimedia workstation by adding a Gold 3GHz F-Connector along with Hubbell's extensive line of AV connectors, loaded modules, Category rated jacks and fiber connectors.

GENERAL INFORMATION

- Important: Always allow for clearance behind connection location to ensure for proper bend radius.
- Gold Plating: Gold plating encapsulates the connectors base metal (brass), preventing oxidation/corrosion from forming. It also has a more transparent (signal) conductive path over nickel (3x), which is closer to the copper over which it is transmitting.

APPLICATIONS

- TV, CCTV, CATV and satellites
- Home theaters and entertainment systems
- Security and surveillance systems



ORDERING INFORMATION




Hubbell iSTATION F-Connector Gold 3GHz

Description	Unit of Measure	Catalog Number
Pass-thru, F/F coupler	1 per bag	SFF3Gxx

xx = Color: **AL** (Almond), **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **OW** (Office White), and **W** (White)



DIMENSIONS



ACCESSORIES

Hubbell iSTATION Modular Face Plate Frames

	1-Gang	2-Gang
Office White	IMF1xx	IMF2xx

xx = Color: **AL** (Almond), **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **OW** (Office White), and **W** (White)



USB 2.0 Full Speed 110 Extenders

Description	Color	Catalog Number
Module 1-U	Black	IMU1101BK
	Electric Ivory	IMU1101EI
	Gray	IMU1101GY
	Office White	IMU1101OW
	White	IMU1101W



Hubbell iSTATION Keystone Modules

Description	Catalog Number
Keystone, 2-port, flat, 1-unit	IM2K1xx

xx = Color: **AL** (Almond), **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **OW** (Office White), and **W** (White)



HDMI 110 Extender Modules

Description	Catalog Number
110 UTP 2-unit HDMI extender (pair)	IMH110ST2xx

xx = Color: **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **OW** (Office White), and **W** (White)



Hubbell iSTATION VGA and 3.5mm 110 Extender, 1.5-Unit

Color	Catalog Number
Black	IM15311015BK
Electric Ivory	IM15311015EI
Gray	IM15311015GY
Office White	IM15311015OW
White	IM15311015W

