



CABLE ACCESSORIES 600A Cross Reference



Hubbell®	Description	Cooper®	Elastimold®
625TB	25kV 600a T-Body w/Stud	DT625	K655BLR-N
625TBT	25kV 600a T-Body w/Stud TP	DT625T	K656BLR
625BT-wxx	25kV 600a T-Body Kit	BT625wxx	K655LR-wx
625BT-wxxT	25kV 600a T-Body Kit TP	BT625wxxT	K656LR-wx
625CA-w	25kV 600a Cable Adapter	CA625-w	655CA-w
625LUG-xx	600a Lug, Through Hole	CC6AxxU	03700xxx
625LUG-xxT	600a Lug, Threaded Hole	CC6AxxT	03600xxx
625SA	25kV 600a Stud AL	STUD-A	650SA
625BIP	25kV 600a Insulating Plug	DIP625A	K650BIP
625BIPS	25kV 600a Insulating Plug w/Stud	DIP625A-S	K650BIP-S
615ETP	15kV 600a Bolted Tap Plug	BLRTP615	650ETP
615ETPS	15kV 600a Bolted Tap Plug w/Stud	BLRTP615	650ETP-S
615ETP-wxx	15kV 600a Bolted Tap Plug Kit	BTP615wxx	655ETP-wxx
615ETP-wxxT	15kV 600a Bolted Tap Plug Kit TP	BTP615wxxT	656ETP-wxx
615ETP-wxx-C	15kV 600a Bolted Tap Plug Kit w/ Cap	BTP615wxxC	655ETP-wxx-DRG
615ETP-wxxTC	15kV 600a Bolted Tap Plug Kit w/ Cap TP	BTP615wxxTC	656ETP-wxx-DRG
625ETP	25kV 600a Bolted Tap Plug	BLRTP625	K650ETP
625ETPS	25kV 600a Bolted Tap Plug w/ Stud	BLRTP625	K650ETP-S
625ETP-wxx	25kV 600a Bolted Tap Plug Kit	BTP625wxx	K655ETP-wxx
625ETP-wxxT	25kV 600a Bolted Tap Plug Kit TP	BTP625wxxT	6K656ETP-wxx
625ETP-wxxC	25kV 600a Bolted Tap Plug Kit w/Cap	BTP625wxxC	K655ETP-wxx-DRG
625ETP-wxxTC	25kV 600a Bolted Tap Plug Kit TP w/Cap	BTP625wxxTC	K656ETP-wxx-DRG
615LRTP	15kV 600a Reducing Tap Plug	L RTP615	650LRTPA3
615LRTP-wxx	15kV 600a Reducing Tap Plug Kit	TP615wxx	655LRTP-wxx
615LRTP-wxxT	15kV 600a Reducing Tap Plug Kit TP	TP615wxxT	656LRTP-wxx
615LRTP-wxxC	15kV 600a Reducing Tap Plug Kit w/Cap	TP615wxxC	655LRTP-wxx-DRG
615LRTP-wxxTC	15kV 600a Reducing Tap Plug Kit w/Cap TP	TP615wxxTC	656LRTP-wxx-DRG
625LRTP	25kV 600a Threaded Tap Plug	L RTP625	K650LRTPA2
625LRTP-wxx	25kV 600a Reducing Tap Plug Kit	TP625wxx	K650LRTP-wxx
625LRTP-wxxT	25kV 600a Reducing Tap Plug Kit TP	TP625wxxT	K656LRTP-wxx
625LRTP-wxxC	25kV 600a Reducing Tap Plug Kit w/Cap	TP625wxxC	K650LRTP-wxx-DRG
625LRTP-wxxTC	25kV 600a Reducing Tap Plug Kit TP w/Cap	TP625wxxTC	K656LRTP-wxx-DRG
625IC	25kV 600a Insulating Cap w/Stud	DPC625	K656DR*
625RTW	25kV 600a Reducing Tap Well	n/a	K650RTW
625RTWS	25kV 600a Reducing Tap Well w/Stud	n/a	K650RTW-S
625CP	25kV 600a Connecting Plug	DCP625A	K655CP
625CPS	25kV 600a Connecting Plug w/Stud	DCP625A-S	K650CP-S
625SOP	25kV 600a Standoff Bushing	ISB625A	K650SOP
625SOPS	25kV 600a Standoff Bushing w/Stud	ISB625A-SA	K650SOP-S
625BE	25kV 600a Bushing Extender	DBE625	K655BE-N
625BES	25kV 600a Bushing Extender w/Stud	DBE625SA	K655BE
615BA	15kV 600a Stick-Op Bushing Adapter	DBA615	650BEA3
625BA	25kV 600a Stick-Op Bushing Adapter	DBA625	K650BEA2
625GP	25kV 600a Grounding Plug	GSB625C	650GP
625GPS	25kV 600a Grounding Plug w/Stud	GSB625A-SA	650GP-SP
625SK-52	Elbow Seal 0.95" to 1.94"	CS1	200ECS
625SK-53	Elbow Seal 1.28" to 2.67"	CS2	600ECS
625SK-59	Tape Shield Adapter 0.59" to 1.05"	SA1	n/a
625SK-60	Tape Shield Adapter 0.83" to 1.64"	SA2	200ECSG3
625SK-61	Tape Shield Adapter 1.27" to 2.17"	SA3	600ECSG3
625SK-62	Tape Shield Adapter 1.70" to 2.60"	SA4	n/a
600SW	Spanner Wrench	n/a	600SW

Note : Elastimold® Insulating Cap has a test point.



CABLE ACCESSORIES 600A Cross Reference



Aluminum Compression Lugs

Stranded/ Compressed	Hubbell®	Cooper®	Elastimold®	Richards®
#2	625LUG22	CC6A11U	03700220	P6AL7
#1	625LUG23	CC6A12U	03700230	P6AL8
1/0	625LUG24	CC6A13U	03700240	P6AL9
2/0	625LUG25	CC6A14U	03700250	P6AL10
3/0	625LUG26	CC6A15U	03700260	P6AL11
4/0	625LUG27	CC6A16U	03700270	P6AL12
250	625LUG28	CC6A17U	03700280	P6AL13
300	625LUG29	CC6A18U	03700290	P6AL14
350	625LUG30	CC6A19U	03700300	P6AL15
400	625LUG31	CC6A20U	03700310	P6AL16
450	625LUG32	CC6A21U	03700320	P6AL17
500	625LUG33	CC6A22U	03700330	P6AL18
550	625LUG34	N/A	03700340	P6AL20
600	625LUG35	CC6A23U	03700350	P6AL20
650	625LUG36	CC6A24U	03700360	P6AL21-1
700	625LUG38	CC6A25U	03700380	P6AL22
750	625LUG38	CC6A25U	03700380	P6AL23
800	625LUG39	N/A	03700390	P6AL24
900	625LUG40	CC6A26U	03700400	P6AL26
1000	625LUG41	CC6A27U	03700410	P6AL28
1250	625LUG44	N/A	03700440	P6AL29

Note: For Threaded lug add a T to Hubbell part #

Elastimold is a trademark of Thomas and Betts Corporation. Cooper is a trademark of Cooper Industries, Inc. Richards is a trademark of Richards Manufacturing Co.



Cable Adapter Ranges

Hubbell® / Elastimold® / Richards®			Cooper®		
Size	Min	Max	Size	Min	Max
F	0.640"	0.820"	AB	0.610"	0.970"
G	0.760"	0.950"	CC	0.750"	1.080"
H	0.850"	1.050"			
J	0.980"	1.180"	DD	0.970"	1.310"
K	1.090"	1.310"	EE	1.090"	1.470"
L	1.180"	1.465"			
LM	1.280"	1.430"	FF	1.260"	1.640"
M	1.370"	1.630"	GG	1.360"	1.710"
N	1.515"	1.780"	HH	1.510"	1.850"
P	1.725"	1.935"	JJ	1.700"	1.970"



Deadbreak Junctions

Hubbell®	Description	Cooper®	Elastimold®
625J2	25kV 600a 2-pt Junction	n/a	K650J2-4
625J2B	25kV 600a 2-pt Junction Bracket	DJ625A2B	K650J2
625J2U	25kV 600a 2-pt Junction U-Straps	DJ625A2U	K650J2-5
625J3	25kV 600a 3-pt Junction	n/a	K650J3-4
625J3B	25kV 600a 3-pt Junction Bracket	DJ625A3B	K650J3
625J3U	25kV 600a 3-pt Junction U-Straps	DJ625A3U	K650J3-5
625J4	25kV 600a 4-pt Junction	n/a	K650J4-4
625J4B	25kV 600a 4-pt Junction Bracket	DJ625A4B	K650J4
625J4U	25kV 600a 4-pt Junction U-Straps	DJ625A4U	K650J4-5



E-mail: hpsliterature@hps.hubbell.com
Web: www.hubbellpowersystems.com

Hubbell Power Systems, Inc. • 210 N. Allen St., Centralia, MO 65240 • Phone: 573-682-5521 • fax: 573-682-8714

Note: Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.