



USB-C POWER DELIVERY RECEPTACLES

Now charge laptops and devices faster with high power USB!

Receptacles with fast charging USB-C® Power Delivery (PD) technology provide more power. Users can quickly charge laptops and other larger devices. Phones and tablets can charge up to three to four times faster.

These durable USB chargers/power receptacles deliver convenience, eliminating the need for power adapters while maintaining electrical outlets for higher current requirements.

The USB-C port marked PD (Power Delivery) provides up to 55W of output. The additional Type-C or Type-A port supports USB BC 1.2. Commercial Grade versions are available in various colors.

Features

- Power Delivery USB-C port provides up to 20V, 55W output
- Additional C or A port delivers up to 1.5A/5V, up to 7.5W
- Heavy-duty stainless-steel USB ports rated for 10,000 cycles
- Duplex 125 VAC power receptacles available in 15A or 20A models
- Receptacles feature patented Hubbell tamper-resistant technology

Applications

- | | |
|----------------|---------------|
| • Multi-Family | • Hotels |
| • Universities | • Commercial |
| • Institutions | • Home Office |



MORE POWER, LESS HEAT

Gallium Nitride (GaN) technology with optimized electronic efficiency reduces size and heat, allowing more power



USB-C Power Delivery Receptacles

USB Charger Type C

Description	Color	Commercial Grade	
		15A 125V	20A 125V
Two Type C port configurations, (1) USB-C® Power Delivery port with up to 55W output and (1) USB-C Convenience port 1.5A, 5V output, Tamper-Resistant duplex receptacle, USB ports rated 10,000 cycles.	Black	USBB15CPDBK	USBB20CPDBK
	Brown	USBB15CPD	USBB20CPD
	Gray	USBB15CPDGY	USBB20CPDGY
	Ivory	USBB15CPDI	USBB20CPDI
	Light Almond	USBB15CPDLA	USBB20CPDLA
	White	USBB15CPDW	USBB20CPDW



USBB15CPDBK



USBB15CPD



USBB15CPDGY

USB Charger Combination Type A & C

Description	Color	Commercial Grade	
		15A 125V	20A 125V
(1) USB-C Power Delivery port with up to 55W output and (1) USB Type-A Convenience port 1.5A, 5V output, Tamper-Resistant duplex receptacle, USB ports rated 10,000 cycles.	Black	USBB15ACPDBK	USBB20ACPDBK
	Brown	USBB15ACPD	USBB20ACPD
	Gray	USBB15ACPDGY	USBB20ACPDGY
	Ivory	USBB15ACPDI	USBB20ACPDI
	Light Almond	USBB15ACPDLA	USBB20ACPDLA
	White	USBB15ACPDW	USBB20ACPDW



USBB15ACPDI



USBB15ACPDLA



USBB15ACPDW



A proud member of the Hubbell family.

©2024 Hubbell Incorporated. All rights reserved.
 Bryant and the Bryant logo are registered trademarks or trademarks of Hubbell Incorporated.
 All other trademarks are the property of their respective owners.
hubbell.com/bryant/en | 40 Waterview Drive, Shelton, CT 06484 | 800-323-2792