HUBBELL
Wiring Device-Kellems

Heavy Duty Products, IEC Pin and Sleeve Devices, Switched, IEC 309, Male Plug, 32A 125V, 2-Pole 3-Wire Grounding, NEMA 4X/IP67, Watertight

By Hubbell Wiring Device-Kellems
Catalog # HBLS332P4W

Heavy Duty IEC Pin and Sleeve Switched, IEC 309 Male Plug, 32A 125V, 2-Pole 3-Wire Grounding, NEMA 4X/IP67,Watertight

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a diconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

Catalog Number	HBLS332P4W
Color	Yellow
Number Of Poles	2-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Plug
UPC	783585550824

Electrical Ratings

Amperage Rating	32 A
Current / Amperage Rating	32 A
Voltage Rating	100-130 VAC
Voltage Rating Description	100-130 VAC

Conductor Related

Number Of Wires	3-Wire

Logistics

Carton Quantity	10

Product Assets

Catalogs - WDK Catalog Full 2024
Literature - PULP & PAPER SOLUTIONS
Literature - Pulp & Paper Solutions
Specifications - HBLS332P4W
Warranty - Industrial & Commercial Products
Video - Advantage Series Switch-Rated Pin & Sleeve

©2024 Hubbell Incorporated. All rights reserved