HUBBELL
Wiring Device-Kellems

Heavy Duty Products, IEC Pin and Sleeve, Inlet, Switched, 60A 3-Phase 120/208V AC, 4-Pole 5-Wire Grounding, NEMA4X/IP69K

By Hubbell Wiring Device-Kellems
Catalog # HBLS560B9W

Heavy Duty IEC Pin and Sleeve, Inlet, Switched, 60A 3-Phase 120/208V AC, 4-Pole 5-Wire Grounding, NEMA4X/IP69K

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a diconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

Catalog Number	HBLS560B9W
Color	Blue
Number Of Poles	4-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Inlet
UPC	783585479330

Electrical Ratings

Amperage Rating	60/63 A
Current / Amperage Rating	60/63 A
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208 VAC

Conductor Related

Number Of Wires	5-Wire

Logistics

Carton Quantity	10

Product Assets

Catalogs - WDK Catalog Full 2024
Engineering Drawing - HBLS560B9W AutoCAD Drawing
Installation Manuals - WIRING_PD1304_INSTALLINST
Literature - PULP & PAPER SOLUTIONS
Literature - Pulp & Paper Solutions
Sales Drawings - WDK_HBLS560_DRAWING_PDF
Specifications - HBLS560B9W
Warranty - Industrial & Commercial Products
Video - Advantage Series Switch-Rated Pin & Sleeve

©2024 Hubbell Incorporated. All rights reserved