

HUBBELL

Premise Wiring

MPTL Cobra-Lock™ Coupler Assembly with Outdoor Cable

Spaces are getting more intelligent. Links terminated with modular plugs help accelerate integration of APs, cameras, and other building systems to the IP network.

Hubbell's versatile MPTL assembly with Cobra-Lock termination was designed to tackle all direct-attach applications. The compact coupler provides fast, reliable, and secure installation. Perfect for applications with limited space which can't accept traditional field terminating plugs. Terminate and ensure integrity without special tools.

The MPTL Cobra-Lock coupler with outdoor cable can be tested to MPTL limits and deployed from inside a building, pole, or enclosure to connect to cameras, access points, and any other IP connection outdoors or in harsh environments. Extend your network wherever you need it and support the growing number of edge devices in non-traditional areas with speeds up to 10Gbe.




Features:

- Bootless plug for AP and camera applications with limited space
- C6A shielded performance for full backward compatibility and use with unshielded and shielded applications
- Rugged black UV resistant CM/CMX outdoor rated cable
- High Flex TPE jacket provides protection and flexibility
- Easy to re-terminate
- Non-terminated option for extending horizontal runs
- Verified to Cat6A MPTL limits
- Wires secured under constant pressure
- UL Listed
- Cable Temperature Rating: -40°C - 75°C

Applications:

- Security cameras
- APs
- PoE lighting
- POS terminals
- Building automation systems
- AV over IP
- Industrial automation



Cobra-Lock™ MPTL Solutions

Ordering Information

6A Coupler MPTL Assembly with Cobra-Lock Termination

MPTL Assembly with Outdoor CMX Rated Cable

Description	Catalog No.
MPTL Assembly, CAT6A,Shielded, 18 IN, Black Outdoor Jacket	SCP6AIOBK
MPTL Assembly, CAT6A,Shielded, 3 FT, Black Outdoor Jacket	SCP6AIOBK03
MPTL Assembly, CAT6A,Shielded, 5 FT, Black Outdoor Jacket	SCP6AIOBK05
MPTL Assembly, CAT6A,Shielded, 7 FT, Black Outdoor Jacket	SCP6AIOBK07
MPTL Assembly, CAT6A,Shielded, 10 FT, Black Outdoor Jacket	SCP6AIOBK10
MPTL Assembly, CAT6A,Shielded, 15 FT, Black Outdoor Jacket	SCP6AIOBK15



MPTL Assembly with Indoor CMP Rated Cable

Color	Cable Length				
	18"	3'	5'	7'	10'
Grey	SCP6A	SCP6AGY03	SCP6AGY05	SCP6AGY07	SCP6AGY10
Blue	SCP6AB	SCP6AB03	SCP6AB05	SCP6AB07	SCP6AB10
Black	SCP6ABK	SCP6ABK03	SCP6ABK05	SCP6ABK07	SCP6ABK10
Green	SCP6AGN	SCP6AGN03	SCP6AGN05	SCP6AGN07	SCP6AGN10
White	SCP6AW	SCP6AW03	SCP6AW05	SCP6AW07	SCP6AW10
Orange	SCP6AOR	SCP6AOR03	SCP6AOR05	SCP6AOR07	SCP6AOR10
Yellow	SCP6AY	SCP6AY03	SCP6AY05	SCP6AY07	SCP6AY10
Coupler Only	SC6A				



NEXTSPEED Field Termination MPTL Plugs

Description	Catalog No.
Category 6A	SP6A
Category 6A with 90° Cable Exit	SP6A90
Category 6	SP6
Category 6 with 90° Cable Exit	SP690

