HUBBELL
Wiring Device-Kellems

Patch Cord, Speed Gain, Cat6, Slim, Green, 15′

By Hubbell Wiring Device-Kellems
Catalog # HC6GN15

Patch Cord, Speed Gain, Cat6, Slim, Green, 15′

Features

- Third Party Verified Category 6 Component
- Plug Optimized For High Density Switch Ports
- TSB-155 10 Gig Support
- Qualified to 150% of 802.3bt PoE Current Level

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6GN15
Color	Green
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	Mechanical - Cable to plug tensile strength - 20+ lbs. Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620232225

Dimensions

Length	15 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	ANSI/TIA/EIA-568-C.2 Category 6 Component ISO 11801/60603-7-41 Category 6 Component

Logistics

Carton Quantity	12

Product Assets

Catalog Page - PREM D5 CatalogPage
Catalogs - WDK Catalog Full 2024
Catalogs - Premise Wiring Catalog
Warranty - Industrial & Commercial Products

A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-HC6GN15-SPEC-EN | REV 6/2024