HUBBELL
Wiring Device-Kellems

Copper Solutions, Patch Cords, NEXTSPEED, Cat 6, Slim, 1′ Length, Red

By Hubbell Wiring Device-Kellems
Catalog # HC6R01

Copper Solutions, Patch Cords, NEXTSPEED, Cat 6, Slim, 1′ Length, Red

Features

- Third Party Verified Category 6 Component
- Plug Optimized For High Density Switch Ports
- TSB-155 10 Gig Support
- Qualified to 150% of 802.3bt PoE Current Level

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6R01
Color	Red
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620233321

Dimensions

Length	1 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)

- ANSI/TIA/EIA-568-C.2 Category 6 Component
- ISO 11801/60603-7-41 Category 6 Component

Logistics

Carton Quantity	125

Product Assets

Catalog Page - PREM D5 CatalogPage
Catalogs - Premise Wiring Catalog
Catalogs - WDK Catalog Full 2024
Specifications - HC6R01
Warranty - Industrial & Commercial Products

©2024 Hubbell Incorporated. All rights reserved