

# ISTWLUGB



## RECOMMENDED CRIMP TOOLS AND DIES FOR HUBBELL TERMINATION CONNECTORS

Hubbell Part Number	Nominal Crimp Barrell O.D.	CONDUCTOR SIZE (ALUMINUM ONLY)		EEI	CSA	Anderson Versa-Crimp (Crimps)				BURNDY (Crimps)					BLACKBURN (Crimps)		KEARNEY (Crimps)		KEARNEY (Crimps)	
		Stranded/Compressed	Compact/Solid			VC6-350	VC6	VC6-FT	VC8	INDEX	HAND	Y35 Y45 Y46	Y48B	Y60BHU	HAND	HYD	HAND	HYD	HAND	HYD
B27	0.906"	4/0 - 250	250	11A	--	(4)	(3)	(3)	--	K840 249	W-K840 (6) W-249 (2)	U-249 (2)	--	--	840 (6)	B-49EA (2)	5/8 (4)	5/8 (2)	TU (6)	76 (2) 76H (4)
B30	1.187"	350	500	13A	28	(5)	(4)	(4)	--	316 655 472 705	--	U-316 (4) U-655 (3) U32ART(4) U-705	C-316 (2)	L-316	--	B-80EA (3)	840 (6)	1 1/8-1 (2) 1 1/8-2 (3)	--	96 (2) 96H (4)
B33		500	600			--	--													
B38	1.375"	700-750	750	14A	--	--	--	(4)	(3)	317 327 719	--	U-317 (4) U-327 (4)	C-317 (2) C-327(2)	L-317 L-720	--	B-20AH (3)	--	1 3/16 (4)	--	106 (3) 106H (5)
B41	1.600"	1000	--	--	--	--	--	--	(4)	301 608 724 788	--	C-39ARP(2) U-786	C-608 (2)	L-608 L-724	--	--	--	1 1/2 (5)	--	140 (2) 140H (5)

**NOTES:**

- Wire Brush conductor before inserting into compression connector
- Make sure to completely insert the conductor into the connector
- Do not crimp above the knurled line on the connector
- ( ) Indicates the minimum number of crimps without overlapping indents
- Rotate each successive indent 90° or 180° to prevent bowing



## CABLE ACCESSORIES

1850 Richland Ave. East • Aiken, SC 29801 • Phone: 573-682-5521 • Fax: 573-682-8714  
 E-mail: [hpsliterature@hps.hubbell.com](mailto:hpsliterature@hps.hubbell.com) • Website: <http://www.hubbell.com>

NOTE: Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.